



Main

Range	Prisma
Range compatibility	Prisma G Pack 160
Product or component type	Rail
Accessory / separate part category	Installation accessory
Type of rail	Modular Rear
Installed device	Altistart : ATS01N103/106FT TeSys : fixed GV2 + D or K contactors <= 40 A - horizontal installation TeSys : fixed TeSys U - horizontal installation TeSys : fixed GV3Pxx1 + LC1D40 to D65 - horizontal installation TeSys : fixed D or K contactors <= 40 A - horizontal installation
Poles description	9 x 3P : fixed : GV2 + D or K contactors <= 40 A horizontal installation 9 x 3P : fixed : TeSys U horizontal installation 7 x 3P : fixed : GV3Pxx1 + LC1D40 to D65 horizontal installation 9 x 4P : fixed : D or K contactors <= 40 A horizontal installation

Complementary

Installation description	Floor-standing enclosure - width 600 mm Wall-mounted enclosure - width 600 mm Pack enclosure - width 555 mm
Number of vertical modules [50 mm]	4 module(s) : ATS01N103/106FT in 600 mm Wide floor-standing enclosure 4 module(s) : ATS01N103/106FT in 600 mm Wide wall-mounted enclosure 4 module(s) : ATS01N103/106FT in 555 mm Wide Pack enclosure 3 module(s) : D or K contactors <= 40 A , direct in 600 mm Wide floor-standing enclosure 3 module(s) : D or K contactors <= 40 A , direct in 600 mm Wide wall-mounted enclosure 3 module(s) : D or K contactors <= 40 A , direct in 555 mm Wide Pack enclosure 5 module(s) : GV2 + D or K contactors <= 40 A , direct in 600 mm Wide floor-standing enclosure 5 module(s) : GV2 + D or K contactors <= 40 A , direct in 600 mm Wide wall-mounted enclosure 5 module(s) : GV2 + D or K contactors <= 40 A , direct in 555 mm Wide Pack enclosure 7 module(s) : GV3Pxx1 + LC1D40 to D65 , direct in 600 mm Wide floor-standing enclosure 7 module(s) : GV3Pxx1 + LC1D40 to D65 , direct in 600 mm Wide wall-mounted enclosure 7 module(s) : GV3Pxx1 + LC1D40 to D65 , direct in 555 mm Wide Pack enclosure 5 module(s) : TeSys U , direct in 600 mm Wide floor-standing enclosure 5 module(s) : TeSys U , direct in 600 mm Wide wall-mounted enclosure 5 module(s) : TeSys U , direct in 555 mm Wide Pack enclosure

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

4 module(s) : TeSys U , direct in 600 mm Wide floor-standing enclosure
4 module(s) : TeSys U , direct in 600 mm Wide wall-mounted enclosure
4 module(s) : TeSys U , direct in 555 mm Wide Pack enclosure

9 mm pitches	48
Quantity per set	Set of 1
Height	14.8 mm
Width	600 mm
Depth	128 mm
Product weight	0.16 kg
Colour	Grey
Material	Metal

Environment

Standards	IEC 61439-2 IEC 61439-1
Product certifications	ASEFA

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0807 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------