Product datasheet

Specifications



W600 REAR MODULAR DEVICE RAIL PRISMA G



03004

① Discontinued on: 5 Apr 2023

EAN Code: 3303430030041



Main

| Range | Prisma | |
|---------------------------------------|--|--|
| Range Of Product | Prisma G | |
| Product Or Component Type | Rail | |
| Accessory / Separate Part Category | Installation accessory | |
| Range Compatibility | Prisma Prisma G | |
| Type Of Rail | Modular Rear | |
| Installed Device | Altistart: ATS01N103/106FT TeSys: fixed D or K contactors <= 40 A - horizontal installation TeSys: fixed GV2 + D or K contactors <= 40 A - horizontal installation TeSys: fixed GV3Pxx1 + LC1D40 to D65 - horizontal installation TeSys: fixed TeSys U - horizontal installation | |
| Poles Description | 9 x 4P: fixed D or K contactors <= 40 A horizontal installation 9 x 3P: fixed GV2 + D or K contactors <= 40 A horizontal installation 7 x 3P: fixed GV3Pxx1 + LC1D40 to D65 horizontal installation 9 x 3P: fixed TeSys U horizontal installation | |

Complementary

| Installation Description | Floor-standing enclosure - width 600 mm |
|--------------------------------|---|
| | Wall-mounted enclosure - width 600 mm |
| | Pack enclosure - width 555 mm |
| Number Of Vertical Modules [50 | 4 module(s): ATS01N103/106FT in 600 mm Widefloor-standing enclosure |
| Mm] | 4 module(s): ATS01N103/106FT in 600 mm Widewall-mounted enclosure |
| | 4 module(s): ATS01N103/106FT in 555 mm WidePack enclosure |
| | 3 module(s): D or K contactors <= 40 A, direct in 600 mm Widefloor-standing enclosure |
| | 3 module(s): D or K contactors <= 40 A, direct in 600 mm Widewall-mounted enclosure |
| | 3 module(s): D or K contactors <= 40 A, direct in 555 mm WidePack enclosure |
| | 5 module(s): GV2 + D or K contactors <= 40 A, direct in 600 mm Widefloor-standing enclosure |
| | 5 module(s): GV2 + D or K contactors <= 40 A, direct in 600 mm Widewall-mounted enclosure |
| | 5 module(s): GV2 + D or K contactors <= 40 A, direct in 555 mm WidePack enclosure |
| | 7 module(s): GV3Pxx1 + LC1D40 to D65, direct in 600 mm Widefloor-standing enclosure |
| | 7 module(s): GV3Pxx1 + LC1D40 to D65, direct in 600 mm Widewall-mounted enclosure |
| | 7 module(s): GV3Pxx1 + LC1D40 to D65, direct in 555 mm WidePack enclosure |
| | 5 module(s): TeSys U, direct in 600 mm Widefloor-standing enclosure |
| | 5 module(s): TeSys U, direct in 600 mm Widewall-mounted enclosure |
| | 5 module(s): TeSys U, direct in 555 mm WidePack enclosure |
| | 4 module(s): TeSys U, direct in 600 mm Widefloor-standing enclosure |
| | 4 module(s): TeSys U, direct in 600 mm Widewall-mounted enclosure |
| | 4 module(s): TeSys U, direct in 555 mm WidePack enclosure |

9 Mm Pitches

| Quantity Per Set | Set of 1 | |
|------------------|----------|--|
| Height | 35 mm | |
| Width | 465 mm | |
| Depth | 16 mm | |
| Net Weight | 0.16 kg | |
| Colour | Natural | |
| Material | Metal | |

Environment

| Standards | IEC 61439-1 IEC 61439-2 | |
|------------------------|----------------------------|--|
| Product Certifications | ASEFA | |

Packing Units

| Unit Type Of Package 1 | PCE |
|------------------------------|--------|
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 1.5 cm |
| Package 1 Width | 3.5 cm |
| Package 1 Length | 47 cm |
| Package 1 Weight | 160 g |

Contractual warranty

Warranty 18 months



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

| ⊘ | Reach Free Of Svhc |
|----------|------------------------------------|
| ⊘ | Toxic Heavy Metal Free |
| ⊘ | Mercury Free |
| ⊘ | Rohs Exemption Information Yes |
| Ø | Halogen Free Plastic Parts Product |

Certifications & Standards

| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) |
|--------------------------|--|
| | EU RoHS Declaration |
| China Rohs Regulation | China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure | Product Environmental Profile |