



### Main

Range	Prisma
Range compatibility	Prisma G
Product or component type	Rail
Accessory / separate part category	Installation accessory
Type of rail	Modular Adjustable
Installed device	TeSys : fixed GV3 Altistart : ATS01N103/106FT TeSys : fixed GV2L TeSys : fixed GV2P Compact : fixed NG160 without earth leakage protection - control: toggle TeSys : fixed GV2 + D or K contactors <= 40 A - horizontal installation TeSys : fixed TeSys U - horizontal installation TeSys : fixed GV3Pxx1 + LC1D40 to D65 - horizontal installation TeSys : fixed D or K contactors <= 40 A - horizontal installation Compact : fixed NG160 NA without earth leakage protection - control: toggle Compact : fixed NSXm without earth leakage protection - control: toggle - vertical installation Compact : fixed NSXm with earth leakage protection - control: toggle - vertical installation
Poles description	1 x 3P : fixed : NG160 1 x 3P : fixed : NG160 NA 1 x 4P : fixed : NG160 1 x 4P : fixed : NG160 NA 4 x 3P : fixed : GV2L 4 x 3P : fixed : GV2P 3 x 3P : fixed : GV3 4 x 3P : fixed : GV2 + D or K contactors <= 40 A horizontal installation 3 x 3P : fixed : GV3Pxx1 + LC1D40 to D65 horizontal installation 4 x 3P : fixed : TeSys U horizontal installation 4 x 4P : fixed : D or K contactors <= 40 A horizontal installation 1 x 3P or 4P : fixed : NSXm vertical installation

### Complementary

Installation description	Floor-standing duct - width 300 mm Wall-mounted duct - width 300 mm
Number of vertical modules [50 mm]	4 module(s) : ATS01N103/106FT in 300 mm Wide floor-standing duct 4 module(s) : ATS01N103/106FT in 300 mm Wide wall-mounted duct

3 module(s) : D or K contactors <= 40 A , direct in 300 mm Wide floor-standing duct  
 3 module(s) : D or K contactors <= 40 A , direct in 300 mm Wide wall-mounted duct  
 5 module(s) : GV2 + D or K contactors <= 40 A , direct in 300 mm Wide floor-standing duct  
 5 module(s) : GV2 + D or K contactors <= 40 A , direct in 300 mm Wide wall-mounted duct  
 3 module(s) : GV2L , direct in 300 mm Wide floor-standing duct  
 3 module(s) : GV2L , direct in 300 mm Wide wall-mounted duct  
 3 module(s) : GV2P , direct in 300 mm Wide floor-standing duct  
 3 module(s) : GV2P , direct in 300 mm Wide wall-mounted duct  
 5 module(s) : GV3 , direct in 300 mm Wide floor-standing duct  
 5 module(s) : GV3 , direct in 300 mm Wide wall-mounted duct  
 7 module(s) : GV3Pxx1 + LC1D40 to D65 , direct in 300 mm Wide floor-standing duct  
 7 module(s) : GV3Pxx1 + LC1D40 to D65 , direct in 300 mm Wide wall-mounted duct  
 5 module(s) : NG160 without earth leakage protection , direct in 300 mm Wide floor-standing duct  
 5 module(s) : NG160 without earth leakage protection , direct in 300 mm Wide wall-mounted duct  
 5 module(s) : NG160 NA without earth leakage protection , direct in 300 mm Wide floor-standing duct  
 5 module(s) : NG160 NA without earth leakage protection , direct in 300 mm Wide wall-mounted duct  
 7 module(s) : NSXm without earth leakage protection , direct in 300 mm Wide floor-standing duct  
 7 module(s) : NSXm without earth leakage protection , direct in 300 mm Wide wall-mounted duct  
 7 module(s) : NSXm without earth leakage protection , connection block in 300 mm Wide floor-standing duct  
 7 module(s) : NSXm without earth leakage protection , connection block in 300 mm Wide wall-mounted duct  
 5 module(s) : TeSys U , direct in 300 mm Wide floor-standing duct  
 5 module(s) : TeSys U , direct in 300 mm Wide wall-mounted duct  
 4 module(s) : TeSys U , direct in 300 mm Wide floor-standing duct  
 4 module(s) : TeSys U , direct in 300 mm Wide wall-mounted duct  
 7 module(s) : NSXm with earth leakage protection , direct in 300 mm Wide floor-standing duct  
 7 module(s) : NSXm with earth leakage protection , direct in 300 mm Wide wall-mounted duct  
 7 module(s) : NSXm with earth leakage protection , connection block in 300 mm Wide floor-standing duct  
 7 module(s) : NSXm with earth leakage protection , connection block in 300 mm Wide wall-mounted duct

9 mm pitches	20
Quantity per set	Set of 1
Width	300 mm
Product weight	0.18 kg
Colour	Grey
Material	Metal

## Environment

Standards	IEC 61439-2 IEC 61439-1
Product certifications	ASEFA

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0807 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

## Contractual warranty

Warranty period	18 months
-----------------	-----------