
Product datasheet

Specifications

 → Green Premium[™]



(!) Discontinued

MOUNTING PLATENSX/CVS/ VIGI 250 HZ.FIX. ROT.HANDLE

03031

() Discontinued on: 9 Aug 2023

EAN Code: 3303430030317

Main

Range	Prisma
Range Of Product	Prisma G
Product Or Component Type	Mounting plate
Accessory / Separate Part Category	Installation accessory
Range Compatibility	Prisma Prisma G enclosure
Installation Description	Floor-standing enclosure - width 600mm Wall-mounted enclosure - width 600mm Floor-standing enclosure - width 850mm Floor-standing enclosure + duct - width 600 + 300mm Wall-mounted enclosure + duct - width 600 + 300mm
Installed Device	EasyPact: fixed CVS100160 without earth leakage protection - control: direct front rotary handle - horizontal installation EasyPact: fixed CVS250 without earth leakage protection - control: direct front rotary handle - horizontal installation ComPact: fixed NSX100160 without earth leakage protection - control: direct front rotary handle - horizontal installation ComPact: fixed NSX250 without earth leakage protection - control: direct front rotary handle - horizontal installation EasyPact: fixed CVS100160 with earth leakage protection - control: direct front rotary handle - horizontal installation EasyPact: fixed CVS100160 with earth leakage protection - control: direct front rotary handle - horizontal installation EasyPact: fixed CVS250 with earth leakage protection - control: direct front rotary handle - horizontal installation ComPact: fixed NSX100160 with earth leakage protection - control: direct front rotary handle - horizontal installation ComPact: fixed NSX100160 with earth leakage protection - control: direct front rotary handle - horizontal installation
Poles Description	1 x 3P: fixed CVS100160 horizontal installation 1 x 4P: fixed CVS100160 horizontal installation 1 x 3P: fixed CVS250 horizontal installation 1 x 4P: fixed CVS250 horizontal installation 1 x 3P: fixed NSX100160 horizontal installation 1 x 4P: fixed NSX100160 horizontal installation 1 x 3P: fixed NSX250 horizontal installation 1 x 4P: fixed NSX250 horizontal installation 1 x 4P: fixed NSX250 horizontal installation
Condition Of Using Cable Tie	Need additional plate (2M high) when installation of device is in horizontal

Number Of Vertical Modules [50 Mm]	5 module(s): CVS100160 without earth leakage protection , direct with long terminal shield in 600 mm Widefloor-standing enclosure (cable coming from top or bottom of enclosure)
	5 module(s): CVS100160 without earth leakage protection , direct with long
	terminal shield in 600 mm Widewall-mounted enclosure (cable coming from top or
	bottom of enclosure) 4 module(s): CVS100160 without earth leakage protection , direct with long
	terminal shield in 600 + 300 mm Widefloor-standing enclosure + duct (cable coming
	from top or bottom of enclosure)
	4 module(s): CVS100160 without earth leakage protection , direct with long terminal shield in 600 + 300 mm Widewall-mounted enclosure + duct (cable coming
	from top or bottom of enclosure)
	4 module(s): CVS100160 without earth leakage protection , direct with long
	terminal shield in 850 mm Widefloor-standing enclosure (cable coming from top or
	bottom of enclosure) 5 module(s): CVS250 without earth leakage protection , direct with long terminal
	shield in 600 mm Widefloor-standing enclosure (cable coming from top or bottom of
	enclosure)
	5 module(s): CVS250 without earth leakage protection, direct with long terminal shield in 600 mm Widewall-mounted enclosure (cable coming from top or bottom of enclosure)
	4 module(s): CVS250 without earth leakage protection , direct with long terminal
	shield in 600 + 300 mm Widefloor-standing enclosure + duct (cable coming from top
	or bottom of enclosure) 4 module(s): CVS250 without earth leakage protection , direct with long terminal
	shield in 600 + 300 mm Widewall-mounted enclosure + duct (cable coming from top
	or bottom of enclosure)
	4 module(s): CVS250 without earth leakage protection, direct with long terminal shield in 850 mm Widefloor-standing enclosure (cable coming from top or bottom of
	enclosure)
	4 module(s): NSX100160 without earth leakage protection , direct with long
	terminal shield in 600 + 300 mm Widefloor-standing enclosure + duct (cable coming from top or bottom of enclosure)
	4 module(s): NSX100160 without earth leakage protection , direct with long
	terminal shield in 600 + 300 mm Widewall-mounted enclosure + duct (cable coming
	from top or bottom of enclosure) 5 module(s): NSX100160 without earth leakage protection , direct with long
	terminal shield in 600 mm Widefloor-standing enclosure (cable coming from top or
	bottom of enclosure)
	5 module(s): NSX100160 without earth leakage protection , direct with long terminal shield in 600 mm Widewall-mounted enclosure (cable coming from top or
	bottom of enclosure)
	4 module(s): NSX100160 without earth leakage protection , direct with long
	terminal shield in 850 mm Widefloor-standing enclosure (cable coming from top or bottom of enclosure)
	4 module(s): NSX250 without earth leakage protection , direct with long terminal
	shield in 600 + 300 mm Widefloor-standing enclosure + duct (cable coming from top
	or bottom of enclosure) 4 module(s): NSX250 without earth leakage protection , direct with long terminal
	shield in 600 + 300 mm Widewall-mounted enclosure + duct (cable coming from top
	or bottom of enclosure)
	5 module(s): NSX250 without earth leakage protection, direct with long terminal shield in 600 mm Widefloor-standing enclosure (cable coming from top or bottom of
	enclosure)
	5 module(s): NSX250 without earth leakage protection, direct with long terminal shield in 600 mm Widewall-mounted enclosure (cable coming from top or bottom of enclosure)
	enclosure) 4 module(s): NSX250 without earth leakage protection , direct with long terminal
	shield in 850 mm Widefloor-standing enclosure (cable coming from top or bottom of enclosure)
	5 module(s): CVS100160 with earth leakage protection, direct with long terminal shield in 600 mm Widefloor-standing enclosure (cable coming from top or bottom of
	shield in 600 mm Widefloor-standing enclosure (cable coming from top or bottom of enclosure)
	5 module(s): CVS100160 with earth leakage protection , direct with long terminal
	shield in 600 mm Widewall-mounted enclosure (cable coming from top or bottom of enclosure)
	4 module(s): CVS100160 with earth leakage protection , direct with long terminal shield in 600 + 300 mm Widefloor standing anglesure + dust (cable coming from top
	shield in 600 + 300 mm Widefloor-standing enclosure + duct (cable coming from top or bottom of enclosure)
	4 module(s): CVS100160 with earth leakage protection , direct with long terminal
	shield in 600 + 300 mm Widewall-mounted enclosure + duct (cable coming from top
	or bottom of enclosure) 5 module(s): CVS250 with earth leakage protection , direct with long terminal shield
	in 600 mm Widefloor-standing enclosure (cable coming from top or bottom of enclosure)
	5 module(s): CVS250 with earth leakage protection , direct with long terminal shield in 600 mm Widewall-mounted enclosure (cable coming from top or bottom of
	enclosure) 4 module(s): CVS250 with earth leakage protection , direct with long terminal shield
	in 600 + 300 mm Widefloor-standing enclosure + duct (cable coming from top or

bottom of enclosure)

4 module(s): CVS250 with earth leakage protection , direct with long terminal shield in 600 + 300 mm Widewall-mounted enclosure + duct (cable coming from top or bottom of enclosure)

4 module(s): NSX100...160 with earth leakage protection , direct with long terminal shield in 600 + 300 mm Widefloor-standing enclosure + duct (cable coming from top or bottom of enclosure)

4 module(s): NSX100...160 with earth leakage protection , direct with long terminal shield in 600 + 300 mm Widewall-mounted enclosure + duct (cable coming from top or bottom of enclosure)

5 module(s): NSX100...160 with earth leakage protection , direct with long terminal shield in 600 mm Widefloor-standing enclosure (cable coming from top or bottom of enclosure)

5 module(s): NSX100...160 with earth leakage protection , direct with long terminal shield in 600 mm Widewall-mounted enclosure (cable coming from top or bottom of enclosure)

4 module(s): NSX100...160 with earth leakage protection , direct with long terminal shield in 850 mm Widefloor-standing enclosure (cable coming from top or bottom of enclosure)

4 module(s): NSX250 with earth leakage protection , direct with long terminal shield in 600 + 300 mm Widefloor-standing enclosure + duct (cable coming from top or bottom of enclosure)

4 module(s): NSX250 with earth leakage protection , direct with long terminal shield in 600 + 300 mm Widewall-mounted enclosure + duct (cable coming from top or bottom of enclosure)

5 module(s): NSX250 with earth leakage protection , direct with long terminal shield in 600 mm Widefloor-standing enclosure (cable coming from top or bottom of enclosure)

5 module(s): NSX250 with earth leakage protection , direct with long terminal shield in 600 mm Widewall-mounted enclosure (cable coming from top or bottom of enclosure)

4 module(s): NSX250 with earth leakage protection , direct with long terminal shield in 850 mm Widefloor-standing enclosure (cable coming from top or bottom of enclosure)

IEC 61439-2

Product Certifications

ASEFA

Complementary

Cable Entry	Cut-out plates 0.33 mm top 92 mm
	Cut-out plates 0.31 mm top 42 mm
	Cut-out plates 0.31 mm bottom 42 mm
Protective Treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Surface Finish	Matt
	Smooth
Colour	White (RAL 9001)
Width	600 mm
Height	150 mm
Net Weight	1.08 kg

Functional Unit

600 mm Prisma G floor-standing enclosure EasyPact CVS100...160 without fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 5 0.33 mm 600 mm Prisma G wall-mounted enclosure EasyPact CVS100...160 without fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 5 0.33 mm 600 + 300 mm Prisma G floor-standing enclosure + duct EasyPact CVS100...160 without fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 4 0.31 mm

600 + 300 mm Prisma G wall-mounted enclosure + duct EasyPact CVS100...160 without fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 4 0.31 mm

600 mm Prisma G floor-standing enclosure EasyPact CVS100...160 without fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 5 0.31 mm 600 mm Prisma G wall-mounted enclosure EasyPact CVS100...160 without fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 5 0.31 mm 850 mm Prisma G floor-standing enclosure EasyPact CVS100...160 without fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 4 0.31 mm 600 mm Prisma G floor-standing enclosure EasyPact CVS100...160 without fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 4 0.31 mm 600 mm Prisma G floor-standing enclosure EasyPact CVS100...160 without fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 5 0.33 mm 600 mm Prisma G wall-mounted enclosure EasyPact CVS100...160 without fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 5 0.33 mm 600 + 300 mm Prisma G floor-standing enclosure + duct EasyPact CVS100...160 without fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 5 0.33 mm 600 + 300 mm Prisma G floor-standing enclosure + duct EasyPact CVS100...160 without fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 4 0.31 mm

600 + 300 mm Prisma G wall-mounted enclosure + duct EasyPact CVS100...160 without fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 4 0.31 mm

600 mm Prisma G floor-standing enclosure EasyPact CVS100...160 without fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 5 0.31 mm 600 mm Prisma G wall-mounted enclosure EasyPact CVS100...160 without fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 5 0.31 mm 850 mm Prisma G floor-standing enclosure EasyPact CVS100...160 without fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 4 0.31 mm 600 mm Prisma G floor-standing enclosure EasyPact CVS250 without fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 5 0.33 mm 600 mm Prisma G wall-mounted enclosure EasyPact CVS250 without fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 5 0.33 mm 600 + 300 mm Prisma G floor-standing enclosure + duct EasyPact CVS250 without fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 5 0.33 mm 600 + 300 mm Prisma G floor-standing enclosure + duct EasyPact CVS250 without fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 5 0.33 mm 600 + 300 mm Prisma G floor-standing enclosure + duct EasyPact CVS250 without fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 4 0.31 mm

600 + 300 mm Prisma G wall-mounted enclosure + duct EasyPact CVS250 without fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 4 0.31 mm

600 mm Prisma G floor-standing enclosure EasyPact CVS250 without fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 5 0.31 mm 600 mm Prisma G wall-mounted enclosure EasyPact CVS250 without fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 5 0.31 mm 850 mm Prisma G floor-standing enclosure EasyPact CVS250 without fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 4 0.31 mm 600 mm Prisma G floor-standing enclosure EasyPact CVS250 without fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 5 0.33 mm 600 mm Prisma G wall-mounted enclosure EasyPact CVS250 without fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 5 0.33 mm 600 + 300 mm Prisma G floor-standing enclosure + duct EasyPact CVS250 without fixed direct fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 4 0.31 mm 600 + 300 mm Prisma G floor-standing enclosure + duct EasyPact CVS250 without fixed direct fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 4 0.31 mm 600 + 300 mm Prisma G floor-standing enclosure + duct EasyPact CVS250 without fixed direct fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 4 0.31 mm

600 + 300 mm Prisma G wall-mounted enclosure + duct EasyPact CVS250 without fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 4 0.31 mm

600 mm Prisma G floor-standing enclosure EasyPact CVS250 without fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 5 0.31 mm 600 mm Prisma G wall-mounted enclosure EasyPact CVS250 without fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 5 0.31 mm 850 mm Prisma G floor-standing enclosure EasyPact CVS250 without fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 4 0.31 mm 600 + 300 mm Prisma G floor-standing enclosure + duct ComPact NSX100...160 without fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 4 0.31 mm

600 + 300 mm Prisma G wall-mounted enclosure + duct ComPact NSX100...160 without fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 4 0.31 mm

600 mm Prisma G floor-standing enclosure ComPact NSX100...160 without fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 5 0.33 mm 600 mm Prisma G wall-mounted enclosure ComPact NSX100...160 without fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 5 0.33 mm 600 mm Prisma G floor-standing enclosure ComPact NSX100...160 without fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 5 0.33 mm 600 mm Prisma G wall-mounted enclosure ComPact NSX100...160 without fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 5 0.31 mm 850 mm Prisma G floor-standing enclosure ComPact NSX100...160 without fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 5 0.31 mm 850 mm Prisma G floor-standing enclosure ComPact NSX100...160 without fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 5 0.31 mm

600 + 300 mm Prisma G floor-standing enclosure + duct ComPact NSX100...160 without fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 4 0.31 mm

600 + 300 mm Prisma G wall-mounted enclosure + duct ComPact NSX100...160 without fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 4 0.31 mm

600 mm Prisma G floor-standing enclosure ComPact NSX100...160 without fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 5 0.33 mm 600 mm Prisma G wall-mounted enclosure ComPact NSX100...160 without fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 5 0.33 mm 600 mm Prisma G floor-standing enclosure ComPact NSX100...160 without fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 5 0.31 mm 600 mm Prisma G wall-mounted enclosure ComPact NSX100...160 without fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 5 0.31 mm 600 mm Prisma G wall-mounted enclosure ComPact NSX100...160 without fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 5 0.31 mm 850 mm Prisma G floor-standing enclosure ComPact NSX100...160 without fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 4 0.31 mm 850 mm Prisma G floor-standing enclosure ComPact NSX100...160 without fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 4 0.31 mm 600 + 300 mm Prisma G floor-standing enclosure + duct ComPact NSX250 without fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 4 0.31 mm

600 + 300 mm Prisma G wall-mounted enclosure + duct ComPact NSX250 without fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 4 0.31 mm

600 mm Prisma G floor-standing enclosure ComPact NSX250 without fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 5 0.33 mm 600 mm Prisma G wall-mounted enclosure ComPact NSX250 without fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 5 0.33 mm 600 mm Prisma G floor-standing enclosure ComPact NSX250 without fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 5 0.31 mm 600 mm Prisma G wall-mounted enclosure ComPact NSX250 without fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 5 0.31 mm 600 mm Prisma G wall-mounted enclosure ComPact NSX250 without fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 5 0.31 mm 850 mm Prisma G floor-standing enclosure ComPact NSX250 without fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 4 0.31 mm 600 + 300 mm Prisma G floor-standing enclosure + duct ComPact NSX250 without fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 4 0.31 mm

600 + 300 mm Prisma G wall-mounted enclosure + duct ComPact NSX250 without fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 4 0.31 mm

600 mm Prisma G floor-standing enclosure ComPact NSX250 without fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 5 0.33 mm 600 mm Prisma G wall-mounted enclosure ComPact NSX250 without fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 5 0.33 mm 600 mm Prisma G floor-standing enclosure ComPact NSX250 without fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 5 0.31 mm 600 mm Prisma G wall-mounted enclosure ComPact NSX250 without fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 5 0.31 mm 850 mm Prisma G floor-standing enclosure ComPact NSX250 without fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 4 0.31 mm 600 mm Prisma G floor-standing enclosure EasyPact CVS100...160 with fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 5 0.33 mm 600 mm Prisma G wall-mounted enclosure EasyPact CVS100...160 with fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 5 0.33 mm 600 + 300 mm Prisma G floor-standing enclosure + duct EasyPact CVS100...160 with fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 4 0.31 mm

600 + 300 mm Prisma G wall-mounted enclosure + duct EasyPact CVS100...160 with fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 4 0.31 mm

600 mm Prisma G floor-standing enclosure EasyPact CVS100...160 with fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 5 0.31 mm 600 mm Prisma G wall-mounted enclosure EasyPact CVS100...160 with fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 5 0.31 mm 600 mm Prisma G floor-standing enclosure EasyPact CVS100...160 with fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 5 0.33 mm 600 mm Prisma G wall-mounted enclosure EasyPact CVS100...160 with fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 5 0.33 mm 600 + 300 mm Prisma G floor-standing enclosure + duct EasyPact CVS100...160 with fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 5 0.33 mm 600 + 300 mm Prisma G floor-standing enclosure + duct EasyPact CVS100...160 with fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 5 0.33 mm 600 + 300 mm Prisma G floor-standing enclosure + duct EasyPact CVS100...160 with fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 5 0.33 mm 600 + 300 mm Prisma G floor-standing enclosure + duct EasyPact CVS100...160 with fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 4 0.31 mm

600 + 300 mm Prisma G wall-mounted enclosure + duct EasyPact CVS100...160 with fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 4 0.31 mm

600 mm Prisma G floor-standing enclosure EasyPact CVS100...160 with fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 5 0.31 mm 600 mm Prisma G wall-mounted enclosure EasyPact CVS100...160 with fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 5 0.31 mm 600 mm Prisma G floor-standing enclosure EasyPact CVS250 with fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 5 0.33 mm 600 mm Prisma G wall-mounted enclosure EasyPact CVS250 with fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 5 0.33 mm

600 + 300 mm Prisma G floor-standing enclosure + duct EasyPact CVS250 with fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 4 0.31 mm

600 + 300 mm Prisma G wall-mounted enclosure + duct EasyPact CVS250 with fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 4 0.31 mm 600 mm Prisma G floor-standing enclosure EasyPact CVS250 with fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 5 0.31 mm 600 mm Prisma G wall-mounted enclosure EasyPact CVS250 with fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 5 0.31 mm 600 mm Prisma G wall-mounted enclosure EasyPact CVS250 with fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 5 0.31 mm 600 mm Prisma G floor-standing enclosure EasyPact CVS250 with fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 5 0.33 mm 600 mt Prisma G wall-mounted enclosure EasyPact CVS250 with fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 5 0.33 mm 600 + 300 mm Prisma G floor-standing enclosure + duct EasyPact CVS250 with fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 4 0.31 mm

600 + 300 mm Prisma G wall-mounted enclosure + duct EasyPact CVS250 with fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 4 0.31 mm 600 mm Prisma G floor-standing enclosure EasyPact CVS250 with fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 5 0.31 mm 600 mm Prisma G wall-mounted enclosure EasyPact CVS250 with fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 5 0.31 mm 600 + 300 mm Prisma G floor-standing enclosure + duct ComPact NSX100...160 with fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 4

0.31 mm 600 + 300 mm Prisma G wall-mounted enclosure + duct ComPact NSX100...160 with

fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 4 0.31 mm

600 mm Prisma G floor-standing enclosure ComPact NSX100...160 with fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 5 0.33 mm 600 mm Prisma G wall-mounted enclosure ComPact NSX100...160 with fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 5 0.33 mm 600 mm Prisma G floor-standing enclosure ComPact NSX100...160 with fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 5 0.31 mm 600 mm Prisma G wall-mounted enclosure ComPact NSX100...160 with fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 5 0.31 mm 800 mm Prisma G wall-mounted enclosure ComPact NSX100...160 with fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 5 0.31 mm 850 mm Prisma G floor-standing enclosure ComPact NSX100...160 with fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 5 0.31 mm

600 + 300 mm Prisma G floor-standing enclosure + duct ComPact NSX100...160 with fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 4 0.31 mm

600 + 300 mm Prisma G wall-mounted enclosure + duct ComPact NSX100...160 with fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 4 0.31 mm

600 mm Prisma G floor-standing enclosure ComPact NSX100...160 with fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 5 0.33 mm 600 mm Prisma G wall-mounted enclosure ComPact NSX100...160 with fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 5 0.33 mm 600 mm Prisma G floor-standing enclosure ComPact NSX100...160 with fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 5 0.31 mm 600 mm Prisma G wall-mounted enclosure ComPact NSX100...160 with fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 5 0.31 mm 850 mm Prisma G floor-standing enclosure ComPact NSX100...160 with fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 4 0.31 mm 600 + 300 mm Prisma G floor-standing enclosure + duct ComPact NSX250 with fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 4 0.31 mm 600 + 300 mm Prisma G wall-mounted enclosure + duct ComPact NSX250 with fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 4 0.31 mm 600 mm Prisma G floor-standing enclosure ComPact NSX250 with fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 5 0.33 mm 600 mm Prisma G wall-mounted enclosure ComPact NSX250 with fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 5 0.33 mm 600 mm Prisma G floor-standing enclosure ComPact NSX250 with fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 5 0.31 mm 600 mm Prisma G wall-mounted enclosure ComPact NSX250 with fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 5 0.31 mm 850 mm Prisma G floor-standing enclosure ComPact NSX250 with fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 4 0.31 mm 600 + 300 mm Prisma G floor-standing enclosure + duct ComPact NSX250 with fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 4 0.31 mm 600 + 300 mm Prisma G wall-mounted enclosure + duct ComPact NSX250 with fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 4 0.31 mm 600 mm Prisma G floor-standing enclosure ComPact NSX250 with fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 5 0.33 mm 600 mm Prisma G wall-mounted enclosure ComPact NSX250 with fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 5 0.33 mm 600 mm Prisma G floor-standing enclosure ComPact NSX250 with fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 5 0.31 mm 600 mm Prisma G wall-mounted enclosure ComPact NSX250 with fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 5 0.31 mm

850 mm Prisma G floor-standing enclosure ComPact NSX250 with fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 4 0.31 mm

Packing Units

PCE
1
3.500 cm
18.500 cm
47.000 cm
1.100 kg
\$04
16
30.000 cm
40.000 cm
60.000 cm
18.650 kg
P12
32
45.000 cm
80.000 cm
120.000 cm
35.800 kg

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes
Halogen Free Plastic Parts Product

Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
	Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile