



### Main

Range	Prisma
Range compatibility	Prisma G
Product or component type	Mounting plate
Accessory / separate part category	Installation accessory
Installed device	<p>Compact : fixed NSX100...160 without earth leakage protection - control: direct front rotary handle - horizontal installation</p> <p>Compact : fixed NSX250 without earth leakage protection - control: direct front rotary handle - horizontal installation</p> <p>Easypact : fixed CVS100...160 without earth leakage protection - control: direct front rotary handle - horizontal installation</p> <p>Easypact : fixed CVS250 without earth leakage protection - control: direct front rotary handle - horizontal installation</p> <p>Compact : fixed NSX100...160 with earth leakage protection - control: direct front rotary handle - horizontal installation</p> <p>Compact : fixed NSX250 with earth leakage protection - control: direct front rotary handle - horizontal installation</p> <p>Easypact : fixed CVS100...160 with earth leakage protection - control: direct front rotary handle - horizontal installation</p> <p>Easypact : fixed CVS250 with earth leakage protection - control: direct front rotary handle - horizontal installation</p>
Poles description	<p>1 x 3P : fixed : NSX100...160 horizontal installation</p> <p>1 x 4P : fixed : NSX100...160 horizontal installation</p> <p>1 x 3P : fixed : NSX250 horizontal installation</p> <p>1 x 4P : fixed : NSX250 horizontal installation</p> <p>1 x 4P : fixed : CVS100...160 horizontal installation</p> <p>1 x 3P : fixed : CVS100...160 horizontal installation</p> <p>1 x 4P : fixed : CVS250 horizontal installation</p> <p>1 x 3P : fixed : CVS250 horizontal installation</p>

### Complementary

Installation description	<p>Floor-standing enclosure - width 600 mm</p> <p>Wall-mounted enclosure - width 600 mm</p> <p>Floor-standing enclosure - width 850 mm</p> <p>Floor-standing enclosure + duct - width 600 + 300 mm</p> <p>Wall-mounted enclosure + duct - width 600 + 300 mm</p>
--------------------------	--

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications



Condition of using cable tie	Need additional plate (2M high) when installation of device is in horizontal
Height	150 mm
Product weight	1.08 kg
Surface finish	Matt Smooth
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White RAL 9001

### Environment

Standards	IEC 61439-2
Product certifications	ASEFA

### Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0807 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

### Contractual warranty

Warranty period	18 months
-----------------	-----------