




Price* : 36.17 GBP



Main

Range	Prisma
Range compatibility	Prisma G
Product or component type	Mounting plate
Accessory / separate part category	Installation accessory
Installed device	<p>Compact : fixed NSX100...160 without earth leakage protection - control: direct front rotary handle - vertical installation</p> <p>Compact : fixed NSX250 without earth leakage protection - control: direct front rotary handle - vertical installation</p> <p>Easypact : fixed CVS100...160 without earth leakage protection - control: direct front rotary handle - vertical installation</p> <p>Easypact : fixed CVS250 without earth leakage protection - control: direct front rotary handle - vertical installation</p> <p>Compact : fixed NSX100...160 with earth leakage protection - control: direct front rotary handle - vertical installation</p> <p>Compact : fixed NSX250 with earth leakage protection - control: direct front rotary handle - vertical installation</p> <p>Easypact : fixed CVS100...160 with earth leakage protection - control: direct front rotary handle - vertical installation</p> <p>Easypact : fixed CVS250 with earth leakage protection - control: direct front rotary handle - vertical installation</p>
Poles description	<p>4 x 3P : fixed : NSX100...160 vertical installation</p> <p>4 x 3P : fixed : NSX250 vertical installation</p> <p>4 x 3P : fixed : CVS100...160 vertical installation</p> <p>4 x 3P : fixed : CVS250 vertical installation</p> <p>3 x 4P : fixed : NSX100...160 vertical installation</p> <p>3 x 4P : fixed : NSX250 vertical installation</p> <p>3 x 4P : fixed : CVS100...160 vertical installation</p> <p>3 x 4P : fixed : CVS250 vertical installation</p>

Complementary

Installation description	<p>Floor-standing enclosure - width 600 mm</p> <p>Wall-mounted enclosure - width 600 mm</p>
Number of vertical modules [50 mm]	9 module(s) : CVS100...160 without earth leakage protection , direct with long terminal shield in 600 mm Wide floor-standing enclosure (cable coming from top or bottom of enclosure)

9 module(s) : CVS100...160 without earth leakage protection , direct with long terminal shield in 600 mm Wide wall-mounted enclosure (cable coming from top or bottom of enclosure)
 11 module(s) : CVS250 without earth leakage protection , direct with long terminal shield in 600 mm Wide floor-standing enclosure (cable coming from top or bottom of enclosure)
 11 module(s) : CVS250 without earth leakage protection , direct with long terminal shield in 600 mm Wide wall-mounted enclosure (cable coming from top or bottom of enclosure)
 9 module(s) : NSX100...160 without earth leakage protection , direct with long terminal shield in 600 mm Wide floor-standing enclosure (cable coming from top or bottom of enclosure)
 9 module(s) : NSX100...160 without earth leakage protection , direct with long terminal shield in 600 mm Wide wall-mounted enclosure (cable coming from top or bottom of enclosure)
 11 module(s) : NSX250 without earth leakage protection , direct with long terminal shield in 600 mm Wide floor-standing enclosure (cable coming from top or bottom of enclosure)
 11 module(s) : NSX250 without earth leakage protection , direct with long terminal shield in 600 mm Wide wall-mounted enclosure (cable coming from top or bottom of enclosure)
 10 module(s) : CVS100...160 with earth leakage protection , direct with long terminal shield in 600 mm Wide floor-standing enclosure (cable coming from top or bottom of enclosure)
 10 module(s) : CVS100...160 with earth leakage protection , direct with long terminal shield in 600 mm Wide wall-mounted enclosure (cable coming from top or bottom of enclosure)
 13 module(s) : CVS250 with earth leakage protection , direct with long terminal shield in 600 mm Wide floor-standing enclosure (cable coming from top or bottom of enclosure)
 13 module(s) : CVS250 with earth leakage protection , direct with long terminal shield in 600 mm Wide wall-mounted enclosure (cable coming from top or bottom of enclosure)
 10 module(s) : NSX100...160 with earth leakage protection , direct with long terminal shield in 600 mm Wide floor-standing enclosure (cable coming from top or bottom of enclosure)
 10 module(s) : NSX100...160 with earth leakage protection , direct with long terminal shield in 600 mm Wide wall-mounted enclosure (cable coming from top or bottom of enclosure)
 13 module(s) : NSX250 with earth leakage protection , direct with long terminal shield in 600 mm Wide floor-standing enclosure (cable coming from top or bottom of enclosure)
 13 module(s) : NSX250 with earth leakage protection , direct with long terminal shield in 600 mm Wide wall-mounted enclosure (cable coming from top or bottom of enclosure)

Condition of using cable tie	Need additional plate (1M high) when installation of device is in vertical
Height	150 mm
Product weight	0.84 kg
Surface finish	Matt Smooth
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White RAL 9001

Environment

Standards	IEC 61439-2
Product certifications	ASEFA

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0807 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------