Product datasheet

Specifications





! Discontinued

MOUNTING PLATE NSX/INS-INV250 CHANGEOVER ROT.HAND

03043

! Discontinued on: 9 Aug 2023

EAN Code: 3303430030430

Main

Range	Prisma
Range Of Product	Prisma G
Product Or Component Type	Mounting plate
Accessory / Separate Part Category	Installation accessory
Range Compatibility	Prisma Prisma G enclosure
Installation Description	Floor-standing enclosure - width 600 mm Wall-mounted enclosure - width 600 mm
Installed Device	ComPact: fixed INS250 source changeover - control: direct front rotary handle - vertical installation ComPact: fixed INS250 source changeover - control: mechanical interlock - vertical installation ComPact: fixed INV250 source changeover - control: mechanical interlock - vertical installation Source changeover: fixed NSX100250 source changeover - control: mechanical interlock - vertical installation
Poles Description	1 x 3P: fixed INS250 source changeover vertical installation 1 x 4P: fixed INS250 source changeover vertical installation 1 x 3P: fixed INV250 source changeover vertical installation 1 x 4P: fixed INV250 source changeover vertical installation 1 x 3P: fixed NSX100250 source changeover vertical installation 1 x 4P: fixed NSX100250 source changeover vertical installation
Condition Of Using Cable Tie	Need additional plate (1M high) when installation of device is in vertical
Number Of Vertical Modules [50 Mm]	10 module(s): INS250 source changeover, front connection in 600 mm Widefloor- standing enclosure (cable coming from top or bottom of enclosure) 10 module(s): INS250 source changeover, front connection in 600 mm Widewall- mounted enclosure (cable coming from top or bottom of enclosure) 10 module(s): INV250 source changeover, front connection in 600 mm Widefloor- standing enclosure (cable coming from top or bottom of enclosure) 10 module(s): INV250 source changeover, front connection in 600 mm Widewall- mounted enclosure (cable coming from top or bottom of enclosure) 11 module(s): NSX100250 source changeover, front connection in 600 mm Widefloor-standing enclosure (cable coming from top or bottom of enclosure) 11 module(s): NSX100250 source changeover, front connection in 600 mm Widewall-mounted enclosure (cable coming from top or bottom of enclosure)
Standards	IEC 61439-2
Product Certifications	ASEFA

Complementary

Cable Entry	Cut-out plates 0.37 mm top or bottom 192 mm
Protective Treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Surface Finish	Matt Smooth

26 Apr 2024 Life Is On Schneider

Colour	White (RAL 9001)
Width	600 mm
Height	200 mm
Net Weight	1.37 kg
Functional Unit	600 mm Prisma G floor-standing enclosure ComPact INS250 source changeover
	fixed direct front rotary handle vertical 3P 1 front connection 10 0.37 mm
	600 mm Prisma G wall-mounted enclosure ComPact INS250 source changeover
	fixed direct front rotary handle vertical 3P 1 front connection 10 0.37 mm
	600 mm Prisma G floor-standing enclosure ComPact INS250 source changeover
	fixed direct front rotary handle vertical 4P 1 front connection 10 0.37 mm
	600 mm Prisma G wall-mounted enclosure ComPact INS250 source changeover
	fixed direct front rotary handle vertical 4P 1 front connection 10 0.37 mm
	600 mm Prisma G floor-standing enclosure ComPact INS250 source changeover
	fixed mechanical interlock vertical 3P 1 front connection 10 0.37 mm
	600 mm Prisma G wall-mounted enclosure ComPact INS250 source changeover
	fixed mechanical interlock vertical 3P 1 front connection 10 0.37 mm
	600 mm Prisma G floor-standing enclosure ComPact INS250 source changeover
	fixed mechanical interlock vertical 4P 1 front connection 10 0.37 mm
	600 mm Prisma G wall-mounted enclosure ComPact INS250 source changeover
	fixed mechanical interlock vertical 4P 1 front connection 10 0.37 mm
	600 mm Prisma G floor-standing enclosure ComPact INV250 source changeover
	fixed mechanical interlock vertical 3P 1 front connection 10 0.37 mm
	600 mm Prisma G wall-mounted enclosure ComPact INV250 source changeover
	fixed mechanical interlock vertical 3P 1 front connection 10 0.37 mm
	600 mm Prisma G floor-standing enclosure ComPact INV250 source changeover
	fixed mechanical interlock vertical 4P 1 front connection 10 0.37 mm
	600 mm Prisma G wall-mounted enclosure ComPact INV250 source changeover
	fixed mechanical interlock vertical 4P 1 front connection 10 0.37 mm
	600 mm Prisma G floor-standing enclosure source changeover NSX100250 source
	changeover fixed mechanical interlock vertical 3P 1 front connection 11 0.37 mm
	600 mm Prisma G wall-mounted enclosure source changeover NSX100250 source
	changeover fixed mechanical interlock vertical 3P 1 front connection 11 0.37 mm
	600 mm Prisma G floor-standing enclosure source changeover NSX100250 source
	about a constitution of the description of the second section 4.4.0.07 and

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.0 cm
Package 1 Width	22.5 cm
Package 1 Length	47.0 cm
Package 1 Weight	1.37 kg
Unit Type Of Package 2	S04
Number Of Units In Package 2	14
Package 2 Height	30.0 cm
Package 2 Width	40.0 cm
Package 2 Length	60.0 cm
Package 2 Weight	19.883 kg

changeover fixed mechanical interlock vertical 4P 1 front connection 11 0.37 mm

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc
⊘	Toxic Heavy Metal Free
⊘	Mercury Free
⊘	Rohs Exemption Information Yes
Ø	Halogen Free Plastic Parts Product

Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile