



Main

Range	Prisma
Range compatibility	Prisma G duct Prisma P
Product or component type	Mounting plate
Accessory / separate part category	Installation accessory
Installed device	<p>Easypact: fixed CVS100...160 without earth leakage protection - control: direct front rotary handle - vertical installation</p> <p>Easypact: fixed CVS250 without earth leakage protection - control: direct front rotary handle - vertical installation</p> <p>Compact: fixed NSX100...160 without earth leakage protection - control: direct front rotary handle - vertical installation</p> <p>Compact: fixed NSX250 without earth leakage protection - control: direct front rotary handle - vertical installation</p> <p>Compact: fixed NSX100...160 without earth leakage protection - control: motor mechanism - vertical installation</p> <p>Compact: plug-in NSX100...160 without earth leakage protection - control: direct front rotary handle - vertical installation</p> <p>Compact: plug-in NSX100...160 without earth leakage protection - control: motor mechanism - vertical installation</p> <p>Compact: fixed NSX250 without earth leakage protection - control: motor mechanism - vertical installation</p> <p>Compact: plug-in NSX250 without earth leakage protection - control: direct front rotary handle - vertical installation</p> <p>Compact: plug-in NSX250 without earth leakage protection - control: motor mechanism - vertical installation</p>
Poles description	<p>1 x 3P: fixed CVS100...160 vertical installation</p> <p>1 x 4P: fixed CVS100...160 vertical installation</p> <p>1 x 3P: fixed CVS250 vertical installation</p> <p>1 x 4P: fixed CVS250 vertical installation</p> <p>1 x 3P: fixed NSX100...160 vertical installation</p> <p>1 x 4P: fixed NSX100...160 vertical installation</p> <p>1 x 3P: plug-in NSX100...160 vertical installation</p> <p>1 x 4P: plug-in NSX100...160 vertical installation</p> <p>1 x 3P: fixed NSX250 vertical installation</p> <p>1 x 4P: fixed NSX250 vertical installation</p> <p>1 x 3P: plug-in NSX250 vertical installation</p> <p>1 x 4P: plug-in NSX250 vertical installation</p>

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Complementary

Installation description	Floor-standing duct - width 300 mm Wall-mounted duct - width 300 mm Cubicle - width 400 mm depth 400 mm
Number of vertical modules [50 mm]	9 module(s): CVS100...160 without earth leakage protection , direct with long terminal shield in 300 mm Widefloor-standing duct (cable coming from top or bottom of enclosure) 9 module(s): CVS100...160 without earth leakage protection , direct with long terminal shield in 300 mm Widewall-mounted duct (cable coming from top or bottom of enclosure) 9 module(s): CVS250 without earth leakage protection , direct with long terminal shield in 300 mm Widefloor-standing duct (cable coming from top or bottom of enclosure) 9 module(s): CVS250 without earth leakage protection , direct with long terminal shield in 300 mm Widewall-mounted duct (cable coming from top or bottom of enclosure) 9 module(s): NSX100...160 without earth leakage protection , direct with long terminal shield in 300 mm Widefloor-standing duct (cable coming from top or bottom of enclosure) 9 module(s): NSX100...160 without earth leakage protection , direct with long terminal shield in 300 mm Widewall-mounted duct (cable coming from top or bottom of enclosure) 9 module(s): NSX100...160 without earth leakage protection , front connection in 400 mm Widecubicle 9 module(s): NSX250 without earth leakage protection , direct with long terminal shield in 300 mm Widefloor-standing duct (cable coming from top or bottom of enclosure) 9 module(s): NSX250 without earth leakage protection , direct with long terminal shield in 300 mm Widewall-mounted duct (cable coming from top or bottom of enclosure) 9 module(s): NSX250 without earth leakage protection , front connection in 400 mm Widecubicle
Condition of using cable tie	Need additional plate (1M high) when installation of device is in vertical
Height	300 mm
Net weight	0.5 kg
Surface finish	Matt Smooth
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White (RAL 9001)

Environment

Standards	IEC 61439-2
Product certifications	ASEFA

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	Download RoHS China Declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------