



MOUNTING PLATE NSX/CVS/INS 630 HZ. FIX. TOGGLE

03070

! Discontinued on: 9 Aug 2023

EAN Code: 3303430030706

① Discontinued

Main

Range	Prisma
Range Of Product	Prisma G
Product Or Component Type	Mounting plate
Accessory / Separate Part Category	Installation accessory
Range Compatibility	Prisma Prisma G enclosure
Installation Description	Floor-standing enclosure - width 850 mm Floor-standing enclosure + duct - width 600 + 300 mm Wall-mounted enclosure + duct - width 600 + 300 mm
Installed Device	EasyPact: fixed CVS400 without earth leakage protection - control: toggle - horizontal installation EasyPact: fixed CVS630 without earth leakage protection - control: toggle - horizontal installation EasyPact: fixed EZC400 - control: toggle - horizontal installation EasyPact: fixed EZC630 - control: toggle - horizontal installation ComPact: fixed INS320400 - control: direct front rotary handle - horizontal installation ComPact: fixed INS500630 - control: direct front rotary handle - horizontal installation ComPact: fixed INV320400 - control: direct front rotary handle - horizontal installation ComPact: fixed INV500630 - control: direct front rotary handle - horizontal installation ComPact: fixed NSX400 without earth leakage protection - control: toggle - horizontal installation ComPact: fixed NSX400 without earth leakage protection - control: toggle - horizontal installation
Poles Description	1 x 3P: fixed CVS400 horizontal installation 1 x 4P: fixed CVS400 horizontal installation 1 x 3P: fixed CVS630 horizontal installation 1 x 4P: fixed CVS630 horizontal installation 1 x 4P: fixed EZC400 horizontal installation 1 x 4P: fixed EZC400 horizontal installation 1 x 4P: fixed EZC630 horizontal installation 1 x 4P: fixed EZC630 horizontal installation 1 x 4P: fixed EZC630 horizontal installation 1 x 3P: fixed INS320400 horizontal installation 1 x 4P: fixed INS320400 horizontal installation 1 x 4P: fixed INS500630 horizontal installation 1 x 4P: fixed INS500630 horizontal installation 1 x 4P: fixed INV320400 horizontal installation 1 x 4P: fixed INV320400 horizontal installation 1 x 4P: fixed INV500630 horizontal installation 1 x 4P: fixed INV500630 horizontal installation 1 x 4P: fixed INV500630 horizontal installation 1 x 4P: fixed NSX400 horizontal installation 1 x 4P: fixed NSX400 horizontal installation 1 x 4P: fixed NSX400 horizontal installation

Condition Of Using Cable Tie

Need additional plate (2M high) when installation of device is in horizontal

Number Of Vertical Modules [50 Mm]

- 9 module(s): CVS400 without earth leakage protection , direct with long terminal shield in 600 + 300 mm Widefloor-standing enclosure + duct (cable coming from top of enclosure)
- 9 module(s): CVS400 without earth leakage protection , direct with long terminal shield in 600 + 300 mm Widewall-mounted enclosure + duct (cable coming from top of enclosure)
- 6 module(s): CVS400 without earth leakage protection, direct with long terminal shield in 600 + 300 mm Widefloor-standing enclosure + duct (cable coming from bottom of enclosure)
- 6 module(s): CVS400 without earth leakage protection , direct with long terminal shield in 600 + 300 mm Widewall-mounted enclosure + duct (cable coming from bottom of enclosure)
- 9 module(s): CVS400 without earth leakage protection, direct with long terminal shield in 850 mm Widefloor-standing enclosure (cable coming from top of enclosure) 6 module(s): CVS400 without earth leakage protection, direct with long terminal shield in 850 mm Widefloor-standing enclosure (cable coming from bottom of enclosure)
- 9 module(s): CVS630 without earth leakage protection , direct with long terminal shield in 600 + 300 mm Widefloor-standing enclosure + duct (cable coming from top of enclosure)
- 9 module(s): CVS630 without earth leakage protection, direct with long terminal shield in 600 + 300 mm Widewall-mounted enclosure + duct (cable coming from top of enclosure)
- 6 module(s): CVS630 without earth leakage protection , direct with long terminal shield in 600 + 300 mm Widefloor-standing enclosure + duct (cable coming from bottom of enclosure)
- 6 module(s): CVS630 without earth leakage protection , direct with long terminal shield in 600 + 300 mm Widewall-mounted enclosure + duct (cable coming from bottom of enclosure)
- 9 module(s): CVS630 without earth leakage protection, direct with long terminal shield in 850 mm Widefloor-standing enclosure (cable coming from top of enclosure) 6 module(s): CVS630 without earth leakage protection, direct with long terminal shield in 850 mm Widefloor-standing enclosure (cable coming from bottom of enclosure)
- 9 module(s): EZC400, direct with long terminal shield in 600 + 300 mm Widefloorstanding enclosure + duct (cable coming from top of enclosure)
- 9 module(s): EZC400, direct with long terminal shield in 600 + 300 mm Widewall-mounted enclosure + duct (cable coming from top of enclosure)
- 6 module(s): EZC400, direct with long terminal shield in 600 + 300 mm Widefloorstanding enclosure + duct (cable coming from bottom of enclosure)
- 6 module(s): EZC400, direct with long terminal shield in 600 + 300 mm Widewall-
- mounted enclosure + duct (cable coming from bottom of enclosure)
 9 module(s): EZC630, direct with long terminal shield in 600 + 300 mm Widefloor-
- standing enclosure + duct (cable coming from top of enclosure)
 9 module(s): EZC630, direct with long terminal shield in 600 + 300 mm Widewall-
- mounted enclosure + duct (cable coming from top of enclosure)
 6 module(s): EZC630, direct with long terminal shield in 600 + 300 mm Widefloor-
- standing enclosure + duct (cable coming from bottom of enclosure)
 6 module(s): EZC630, direct with long terminal shield in 600 + 300 mm Widewall-
- mounted enclosure + duct (cable coming from bottom of enclosure)
- 9 module(s): INS320...400, direct with long terminal shield in 600 + 300 mm Widefloor-standing enclosure + duct (cable coming from top of enclosure)
- 9 module(s): INS320...400, direct with long terminal shield in 600 + 300 mm
- Widewall-mounted enclosure + duct (cable coming from top of enclosure)
- 6 module(s): INS320...400, direct with long terminal shield in 600 + 300 mm
- Widefloor-standing enclosure + duct (cable coming from bottom of enclosure)
- 6 module(s): INS320...400, direct with long terminal shield in 600 + 300 mm
- Widewall-mounted enclosure + duct (cable coming from bottom of enclosure)
- 9 module(s): INS320...400, direct with long terminal shield in 850 mm Widefloorstanding enclosure (cable coming from top of enclosure)
- 6 module(s): INS320...400, direct with long terminal shield in 850 mm Widefloorstanding enclosure (cable coming from bottom of enclosure)
- 9 module(s): INS500...630, direct with long terminal shield in 600 + 300 mm
- Widefloor-standing enclosure + duct (cable coming from top of enclosure)
- 9 module(s): INS500...630, direct with long terminal shield in 600 + 300 mm
- Widewall-mounted enclosure + duct (cable coming from top of enclosure)
- 6 module(s): INS500...630, direct with long terminal shield in 600 + 300 mm
- 6 module(s): INS500...630, direct with long terminal shield in 600 + 300 mm
- Widefloor-standing enclosure + duct (cable coming from bottom of enclosure) 6 module(s): INS500...630, direct with long terminal shield in 600 + 300 mm
- Widewall-mounted enclosure + duct (cable coming from bottom of enclosure)

 9 module(s): INS500...630. direct with long terminal shield in 850 mm Widefloor-
- standing enclosure (cable coming from top of enclosure) 6 module(s): INS500...630, direct with long terminal shield in 850 mm Widefloor-
- standing enclosure (cable coming from bottom of enclosure)
 9 module(s): INV320...400, direct with long terminal shield in 600 + 300 mm
 Widefloor-standing enclosure + duct (cable coming from top of enclosure)
- 9 module(s): INV320...400, direct with long terminal shield in 600 + 300 mm Widewall-mounted enclosure + duct (cable coming from top of enclosure)
- 6 module(s): INV320...400, direct with long terminal shield in 600 + 300 mm Widefloor-standing enclosure + duct (cable coming from bottom of enclosure)

6 module(s): INV320...400, direct with long terminal shield in 600 + 300 mm Widewall-mounted enclosure + duct (cable coming from bottom of enclosure) 9 module(s): INV320...400, direct with long terminal shield in 850 mm Widefloorstanding enclosure (cable coming from top of enclosure) 6 module(s): INV320...400, direct with long terminal shield in 850 mm Widefloorstanding enclosure (cable coming from bottom of enclosure) 9 module(s): INV500...630, direct with long terminal shield in 600 + 300 mm Widefloor-standing enclosure + duct (cable coming from top of enclosure) 9 module(s): INV500...630, direct with long terminal shield in 600 + 300 mm Widewall-mounted enclosure + duct (cable coming from top of enclosure) 6 module(s): INV500...630, direct with long terminal shield in 600 + 300 mm Widefloor-standing enclosure + duct (cable coming from bottom of enclosure) 6 module(s): INV500...630, direct with long terminal shield in 600 + 300 mm Widewall-mounted enclosure + duct (cable coming from bottom of enclosure) 9 module(s): INV500...630, direct with long terminal shield in 850 mm Widefloorstanding enclosure (cable coming from top of enclosure) 6 module(s): INV500...630, direct with long terminal shield in 850 mm Widefloorstanding enclosure (cable coming from bottom of enclosure) 9 module(s): NSX400 without earth leakage protection, connection block in 850 mm Widefloor-standing enclosure (cable coming from top of enclosure) 6 module(s): NSX400 without earth leakage protection, connection block in 850 mm Widefloor-standing enclosure (cable coming from bottom of enclosure) 9 module(s): NSX400 without earth leakage protection , connection block in 600 + 300 mm Widefloor-standing enclosure + duct (cable coming from top of enclosure) 9 module(s): NSX400 without earth leakage protection, connection block in 600 + 300 mm Widewall-mounted enclosure + duct (cable coming from top of enclosure) 6 module(s): NSX400 without earth leakage protection, connection block in 600 + 300 mm Widefloor-standing enclosure + duct (cable coming from bottom of enclosure) 6 module(s): NSX400 without earth leakage protection , connection block in 600 + 300 mm Widewall-mounted enclosure + duct (cable coming from bottom of 9 module(s): NSX400 without earth leakage protection, direct with long terminal

shield in 600 + 300 mm Widefloor-standing enclosure + duct (cable coming from top of enclosure)

9 module(s): NSX400 without earth leakage protection , direct with long terminal shield in 600 + 300 mm Widewall-mounted enclosure + duct (cable coming from top of enclosure)

6 module(s): NSX400 without earth leakage protection , direct with long terminal shield in 600 + 300 mm Widefloor-standing enclosure + duct (cable coming from bottom of enclosure)

6 module(s): NSX400 without earth leakage protection , direct with long terminal shield in 600 + 300 mm Widewall-mounted enclosure + duct (cable coming from bottom of enclosure)

9 module(s): NSX400 without earth leakage protection , direct with long terminal shield in 850 mm Widefloor-standing enclosure (cable coming from top of enclosure) 6 module(s): NSX400 without earth leakage protection, direct with long terminal shield in 850 mm Widefloor-standing enclosure (cable coming from bottom of enclosure)

9 module(s): NSX630 without earth leakage protection, connection block in 850 mm Widefloor-standing enclosure (cable coming from top of enclosure)

6 module(s): NSX630 without earth leakage protection, connection block in 850 mm

Widefloor-standing enclosure (cable coming from bottom of enclosure)

9 module(s): NSX630 without earth leakage protection , connection block in 600 + 300 mm Widefloor-standing enclosure + duct (cable coming from top of enclosure) 9 module(s): NSX630 without earth leakage protection , connection block in 600 + 300 mm Widewall-mounted enclosure + duct (cable coming from top of enclosure) 6 module(s): NSX630 without earth leakage protection , connection block in 600 + 300 mm Widefloor-standing enclosure + duct (cable coming from bottom of

6 module(s): NSX630 without earth leakage protection, connection block in 600 + 300 mm Widewall-mounted enclosure + duct (cable coming from bottom of enclosure)

9 module(s): NSX630 without earth leakage protection, direct with long terminal shield in 600 + 300 mm Widefloor-standing enclosure + duct (cable coming from top of enclosure)

9 module(s): NSX630 without earth leakage protection, direct with long terminal shield in 600 + 300 mm Widewall-mounted enclosure + duct (cable coming from top

6 module(s): NSX630 without earth leakage protection, direct with long terminal shield in 600 + 300 mm Widefloor-standing enclosure + duct (cable coming from bottom of enclosure)

6 module(s): NSX630 without earth leakage protection , direct with long terminal shield in 600 + 300 mm Widewall-mounted enclosure + duct (cable coming from bottom of enclosure)

9 module(s): NSX630 without earth leakage protection , direct with long terminal shield in 850 mm Widefloor-standing enclosure (cable coming from top of enclosure) 6 module(s): NSX630 without earth leakage protection, direct with long terminal shield in 850 mm Widefloor-standing enclosure (cable coming from bottom of enclosure)

Standards	IEC 61439-2
Product Certifications	ASEFA

Complementary

Cable Entry	Cut-out plates 0.38 mm top 217 mm Cut-out plates 0.32 mm bottom 67 mm
Protective Treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Surface Finish	Smooth Matt
Colour	White (RAL 9001)
Width	600 mm
Height	250 mm
Net Weight	2.24 kg

Functional Unit

600 + 300 mm Prisma G floor-standing enclosure + duct EasyPact CVS400 without fixed toggle horizontal 3P 1 direct with long terminal shield 9 0.38 mm 600 + 300 mm Prisma G wall-mounted enclosure + duct EasyPact CVS400 without fixed toggle horizontal 3P 1 direct with long terminal shield 9 0.38 mm 600 + 300 mm Prisma G floor-standing enclosure + duct EasyPact CVS400 without fixed toggle horizontal 4P 1 direct with long terminal shield 9 0.38 mm 600 + 300 mm Prisma G wall-mounted enclosure + duct EasyPact CVS400 without fixed toggle horizontal 4P 1 direct with long terminal shield 9 0.38 mm 600 + 300 mm Prisma G floor-standing enclosure + duct EasyPact CVS400 without fixed toggle horizontal 3P 1 direct with long terminal shield 6 0.32 mm 600 + 300 mm Prisma G wall-mounted enclosure + duct EasyPact CVS400 without fixed toggle horizontal 3P 1 direct with long terminal shield 6 0.32 mm 600 + 300 mm Prisma G floor-standing enclosure + duct EasyPact CVS400 without fixed toggle horizontal 4P 1 direct with long terminal shield 6 0.32 mm 600 + 300 mm Prisma G wall-mounted enclosure + duct EasyPact CVS400 without fixed toggle horizontal 4P 1 direct with long terminal shield 6 0.32 mm 850 mm Prisma G floor-standing enclosure EasyPact CVS400 without fixed toggle horizontal 3P 1 direct with long terminal shield 9 0.38 mm 850 mm Prisma G floor-standing enclosure EasyPact CVS400 without fixed toggle horizontal 4P 1 direct with long terminal shield 9 0.38 mm 850 mm Prisma G floor-standing enclosure EasyPact CVS400 without fixed toggle horizontal 3P 1 direct with long terminal shield 6 0.32 mm 850 mm Prisma G floor-standing enclosure EasyPact CVS400 without fixed toggle horizontal 4P 1 direct with long terminal shield 6 0.32 mm 600 + 300 mm Prisma G floor-standing enclosure + duct EasyPact CVS630 without fixed toggle horizontal 3P 1 direct with long terminal shield 9 0.38 mm 600 + 300 mm Prisma G wall-mounted enclosure + duct EasyPact CVS630 without fixed toggle horizontal 3P 1 direct with long terminal shield 9 0.38 mm 600 + 300 mm Prisma G floor-standing enclosure + duct EasyPact CVS630 without fixed toggle horizontal 4P 1 direct with long terminal shield 9 0.38 mm 600 + 300 mm Prisma G wall-mounted enclosure + duct EasyPact CVS630 without fixed toggle horizontal 4P 1 direct with long terminal shield 9 0.38 mm 600 + 300 mm Prisma G floor-standing enclosure + duct EasyPact CVS630 without fixed toggle horizontal 3P 1 direct with long terminal shield 6 0.32 mm 600 + 300 mm Prisma G wall-mounted enclosure + duct EasyPact CVS630 without fixed toggle horizontal 3P 1 direct with long terminal shield 6 0.32 mm 600 + 300 mm Prisma G floor-standing enclosure + duct EasyPact CVS630 without fixed toggle horizontal 4P 1 direct with long terminal shield 6 0.32 mm 600 + 300 mm Prisma G wall-mounted enclosure + duct EasyPact CVS630 without fixed toggle horizontal 4P 1 direct with long terminal shield 6 0.32 mm 850 mm Prisma G floor-standing enclosure EasyPact CVS630 without fixed toggle horizontal 3P 1 direct with long terminal shield 9 0.38 mm 850 mm Prisma G floor-standing enclosure EasyPact CVS630 without fixed toggle horizontal 4P 1 direct with long terminal shield 9 0.38 mm 850 mm Prisma G floor-standing enclosure EasyPact CVS630 without fixed toggle horizontal 3P 1 direct with long terminal shield 6 0.32 mm 850 mm Prisma G floor-standing enclosure EasyPact CVS630 without fixed toggle horizontal 4P 1 direct with long terminal shield 6 0.32 mm 600 + 300 mm Prisma G floor-standing enclosure + duct EasyPact EZC400 fixed toggle horizontal 3P 1 direct with long terminal shield 9 0.38 mm 600 + 300 mm Prisma G wall-mounted enclosure + duct EasyPact EZC400 fixed toggle horizontal 3P 1 direct with long terminal shield 9 0.38 mm 600 + 300 mm Prisma G floor-standing enclosure + duct EasyPact EZC400 fixed toggle horizontal 4P 1 direct with long terminal shield 9 0.38 mm 600 + 300 mm Prisma G wall-mounted enclosure + duct EasyPact EZC400 fixed toggle horizontal 4P 1 direct with long terminal shield 9 0.38 mm 600 + 300 mm Prisma G floor-standing enclosure + duct EasyPact EZC400 fixed toggle horizontal 3P 1 direct with long terminal shield 6 0.32 mm 600 + 300 mm Prisma G wall-mounted enclosure + duct EasyPact EZC400 fixed toggle horizontal 3P 1 direct with long terminal shield 6 0.32 mm 600 + 300 mm Prisma G floor-standing enclosure + duct EasyPact EZC400 fixed toggle horizontal 4P 1 direct with long terminal shield 6 0.32 mm 600 + 300 mm Prisma G wall-mounted enclosure + duct EasyPact EZC400 fixed toggle horizontal 4P 1 direct with long terminal shield 6 0.32 mm 600 + 300 mm Prisma G floor-standing enclosure + duct EasyPact EZC630 fixed toggle horizontal 3P 1 direct with long terminal shield 9 0.38 mm 600 + 300 mm Prisma G wall-mounted enclosure + duct EasyPact EZC630 fixed toggle horizontal 3P 1 direct with long terminal shield 9 0.38 mm 600 + 300 mm Prisma G floor-standing enclosure + duct EasyPact EZC630 fixed toggle horizontal 4P 1 direct with long terminal shield 9 0.38 mm 600 + 300 mm Prisma G wall-mounted enclosure + duct EasyPact EZC630 fixed toggle horizontal 4P 1 direct with long terminal shield 9 0.38 mm 600 + 300 mm Prisma G floor-standing enclosure + duct EasyPact EZC630 fixed toggle horizontal 3P 1 direct with long terminal shield 6 0.32 mm 600 + 300 mm Prisma G wall-mounted enclosure + duct EasyPact EZC630 fixed toggle horizontal 3P 1 direct with long terminal shield 6 0.32 mm 600 + 300 mm Prisma G floor-standing enclosure + duct EasyPact EZC630 fixed toggle horizontal 4P 1 direct with long terminal shield 6 0.32 mm 600 + 300 mm Prisma G wall-mounted enclosure + duct EasyPact EZC630 fixed toggle horizontal 4P 1 direct with long terminal shield 6 0.32 mm

600 + 300 mm Prisma G floor-standing enclosure + duct ComPact INS320...400 fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 9 0.38 mm 600 + 300 mm Prisma G wall-mounted enclosure + duct ComPact INS320...400 fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 9 0.38 mm 600 + 300 mm Prisma G floor-standing enclosure + duct ComPact INS320...400 fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 9 0.38 mm 600 + 300 mm Prisma G wall-mounted enclosure + duct ComPact INS320...400 fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 9 0.38 mm 600 + 300 mm Prisma G floor-standing enclosure + duct ComPact INS320...400 fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 6 0.32 mm 600 + 300 mm Prisma G wall-mounted enclosure + duct ComPact INS320...400 fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 6 0.32 mm 600 + 300 mm Prisma G floor-standing enclosure + duct ComPact INS320...400 fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 6 0.32 mm 600 + 300 mm Prisma G wall-mounted enclosure + duct ComPact INS320...400 fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 6 0.32 mm 850 mm Prisma G floor-standing enclosure ComPact INS320...400 fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 9 0.38 mm 850 mm Prisma G floor-standing enclosure ComPact INS320...400 fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 9 0.38 mm 850 mm Prisma G floor-standing enclosure ComPact INS320...400 fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 6 0.32 mm 850 mm Prisma G floor-standing enclosure ComPact INS320...400 fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 6 0.32 mm 600 + 300 mm Prisma G floor-standing enclosure + duct ComPact INS500...630 fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 9 0.38 mm 600 + 300 mm Prisma G wall-mounted enclosure + duct ComPact INS500...630 fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 9 0.38 mm 600 + 300 mm Prisma G floor-standing enclosure + duct ComPact INS500...630 fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 9 0.38 mm 600 + 300 mm Prisma G wall-mounted enclosure + duct ComPact INS500...630 fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 9 0.38 mm 600 + 300 mm Prisma G floor-standing enclosure + duct ComPact INS500...630 fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 6 0.32 mm 600 + 300 mm Prisma G wall-mounted enclosure + duct ComPact INS500...630 fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 6 0.32 mm 600 + 300 mm Prisma G floor-standing enclosure + duct ComPact INS500...630 fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 6 0.32 mm 600 + 300 mm Prisma G wall-mounted enclosure + duct ComPact INS500...630 fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 6 0.32 mm 850 mm Prisma G floor-standing enclosure ComPact INS500...630 fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 9 0.38 mm 850 mm Prisma G floor-standing enclosure ComPact INS500...630 fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 9 0.38 mm 850 mm Prisma G floor-standing enclosure ComPact INS500...630 fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 6 0.32 mm 850 mm Prisma G floor-standing enclosure ComPact INS500...630 fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 6 0.32 mm 600 + 300 mm Prisma G floor-standing enclosure + duct ComPact INV320...400 fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 9 0.38 mm 600 + 300 mm Prisma G wall-mounted enclosure + duct ComPact INV320...400 fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 9 0.38 mm 600 + 300 mm Prisma G floor-standing enclosure + duct ComPact INV320...400 fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 9 0.38 mm 600 + 300 mm Prisma G wall-mounted enclosure + duct ComPact INV320...400 fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 9 0.38 mm 600 + 300 mm Prisma G floor-standing enclosure + duct ComPact INV320...400 fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 6 0.32 mm 600 + 300 mm Prisma G wall-mounted enclosure + duct ComPact INV320...400 fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 6 0.32 mm 600 + 300 mm Prisma G floor-standing enclosure + duct ComPact INV320...400 fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 6 0.32 mm 600 + 300 mm Prisma G wall-mounted enclosure + duct ComPact INV320...400 fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 6 0.32 mm 850 mm Prisma G floor-standing enclosure ComPact INV320...400 fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 9 0.38 mm 850 mm Prisma G floor-standing enclosure ComPact INV320...400 fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 9 0.38 mm 850 mm Prisma G floor-standing enclosure ComPact INV320...400 fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 6 0.32 mm 850 mm Prisma G floor-standing enclosure ComPact INV320...400 fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 6 0.32 mm 600 + 300 mm Prisma G floor-standing enclosure + duct ComPact INV500...630 fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 9 0.38 mm 600 + 300 mm Prisma G wall-mounted enclosure + duct ComPact INV500...630 fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 9 0.38 mm 600 + 300 mm Prisma G floor-standing enclosure + duct ComPact INV500...630 fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 9 0.38 mm 600 + 300 mm Prisma G wall-mounted enclosure + duct ComPact INV500...630 fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 9 0.38 mm

600 + 300 mm Prisma G floor-standing enclosure + duct ComPact INV500...630 fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 6 0.32 mm 600 + 300 mm Prisma G wall-mounted enclosure + duct ComPact INV500...630 fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 6 0.32 mm 600 + 300 mm Prisma G floor-standing enclosure + duct ComPact INV500...630 fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 6 0.32 mm 600 + 300 mm Prisma G wall-mounted enclosure + duct ComPact INV500...630 fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 6 0.32 mm 850 mm Prisma G floor-standing enclosure ComPact INV500...630 fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 9 0.38 mm 850 mm Prisma G floor-standing enclosure ComPact INV500...630 fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 9 0.38 mm 850 mm Prisma G floor-standing enclosure ComPact INV500...630 fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 6 0.32 mm 850 mm Prisma G floor-standing enclosure ComPact INV500...630 fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 6 0.32 mm 850 mm Prisma G floor-standing enclosure ComPact NSX400 without fixed toggle horizontal 3P 1 connection block 9 0.38 mm

850 mm Prisma G floor-standing enclosure ComPact NSX400 without fixed toggle horizontal 4P 1 connection block 9 0.38 mm

850 mm Prisma G floor-standing enclosure ComPact NSX400 without fixed toggle horizontal 3P 1 connection block 6 0.32 mm

850 mm Prisma G floor-standing enclosure ComPact NSX400 without fixed toggle horizontal 4P 1 connection block 6 0.32 mm

 600 ± 300 mm Prisma G floor-standing enclosure \pm duct ComPact NSX400 without fixed toggle horizontal 3P 1 connection block 9 0.38 mm

600 + 300 mm Prisma G wall-mounted enclosure + duct ComPact NSX400 without fixed toggle horizontal 3P 1 connection block 9 0.38 mm

 600 ± 300 mm Prisma G floor-standing enclosure \pm duct ComPact NSX400 without fixed toggle horizontal 4P 1 connection block 9 0.38 mm

600 + 300 mm Prisma G wall-mounted enclosure + duct ComPact NSX400 without fixed toggle horizontal 4P 1 connection block 9 0.38 mm

600 + 300 mm Prisma G floor-standing enclosure + duct ComPact NSX400 without fixed toggle horizontal 3P 1 connection block 6 0.32 mm

 600 ± 300 mm Prisma G wall-mounted enclosure \pm duct ComPact NSX400 without fixed toggle horizontal 3P 1 connection block 6 0.32 mm

600 + 300 mm Prisma G floor-standing enclosure + duct ComPact NSX400 without fixed toggle horizontal 4P 1 connection block 6 0.32 mm

 600 ± 300 mm Prisma G wall-mounted enclosure \pm duct ComPact NSX400 without fixed toggle horizontal 4P 1 connection block 6 0.32 mm

600 + 300 mm Prisma G floor-standing enclosure + duct ComPact NSX400 without

fixed toggle horizontal 3P 1 direct with long terminal shield 9 0.38 mm 600 + 300 mm Prisma G wall-mounted enclosure + duct ComPact NSX400 without fixed toggle horizontal 3P 1 direct with long terminal shield 9 0.38 mm

 $600+300~\rm mm$ Prisma G floor-standing enclosure + duct ComPact NSX400 without fixed toggle horizontal 4P 1 direct with long terminal shield 9 0.38 mm

 600 ± 300 mm Prisma G wall-mounted enclosure \pm duct ComPact NSX400 without fixed toggle horizontal 4P 1 direct with long terminal shield 9 0.38 mm

600 + 300 mm Prisma G floor-standing enclosure + duct ComPact NSX400 without

fixed toggle horizontal 3P 1 direct with long terminal shield 6 0.32~mm 600 + 300 mm Prisma G wall-mounted enclosure + duct ComPact NSX400 without

fixed toggle horizontal 3P 1 direct with long terminal shield 6 0.32 mm 600 + 300 mm Prisma G floor-standing enclosure + duct ComPact NSX400 without fixed toggle horizontal 4P 1 direct with long terminal shield 6 0.32 mm

600 + 300 mm Prisma G wall-mounted enclosure + duct ComPact NSX400 without fixed toggle horizontal 4P 1 direct with long terminal shield 6 0.32 mm

850 mm Prisma G floor-standing enclosure ComPact NSX400 without fixed toggle horizontal 3P 1 direct with long terminal shield 9 0.38 mm

850 mm Prisma G floor-standing enclosure ComPact NSX400 without fixed toggle horizontal 4P 1 direct with long terminal shield 9 0.38 mm

850 mm Prisma G floor-standing enclosure ComPact NSX400 without fixed toggle horizontal 3P 1 direct with long terminal shield 6 0.32 mm

850 mm Prisma G floor-standing enclosure ComPact NSX400 without fixed toggle horizontal 4P 1 direct with long terminal shield 6 0.32 mm

850 mm Prisma G floor-standing enclosure ComPact NSX630 without fixed toggle horizontal 3P 1 connection block 9 0.38 mm

850 mm Prisma G floor-standing enclosure ComPact NSX630 without fixed toggle horizontal 4P 1 connection block 9 0.38 mm

850~mm Prisma G floor-standing enclosure ComPact NSX630 without fixed toggle horizontal 3P 1 connection block 6 0.32 mm

850~mm Prisma G floor-standing enclosure ComPact NSX630 without fixed toggle horizontal 4P 1 connection block 6 0.32 mm

 600 ± 300 mm Prisma G floor-standing enclosure \pm duct ComPact NSX630 without fixed toggle horizontal 3P 1 connection block 9 0.38 mm

 600 ± 300 mm Prisma G wall-mounted enclosure \pm duct ComPact NSX630 without fixed toggle horizontal 3P 1 connection block 9 0.38 mm

 600 ± 300 mm Prisma G floor-standing enclosure \pm duct ComPact NSX630 without fixed toggle horizontal 4P 1 connection block 9 0.38 mm

 600 ± 300 mm Prisma G wall-mounted enclosure \pm duct ComPact NSX630 without fixed toggle horizontal 4P 1 connection block 9 0.38 mm

600 + 300 mm Prisma G floor-standing enclosure + duct ComPact NSX630 without fixed toggle horizontal 3P 1 connection block 6 0.32 mm

 600 ± 300 mm Prisma G wall-mounted enclosure + duct ComPact NSX630 without fixed toggle horizontal 3P 1 connection block 6 0.32 mm

600 + 300 mm Prisma G floor-standing enclosure + duct ComPact NSX630 without fixed toggle horizontal 4P 1 connection block 6 0.32 mm

 600 ± 300 mm Prisma G wall-mounted enclosure + duct ComPact NSX630 without fixed toggle horizontal 4P 1 connection block 6 0.32 mm

 600 ± 300 mm Prisma G floor-standing enclosure \pm duct ComPact NSX630 without fixed toggle horizontal 3P 1 direct with long terminal shield 9 0.38 mm

 600 ± 300 mm Prisma G wall-mounted enclosure \pm duct ComPact NSX630 without fixed toggle horizontal 3P 1 direct with long terminal shield 9 0.38 mm

 600 ± 300 mm Prisma G floor-standing enclosure \pm duct ComPact NSX630 without fixed toggle horizontal 4P 1 direct with long terminal shield 9 0.38 mm

 600 ± 300 mm Prisma G wall-mounted enclosure \pm duct ComPact NSX630 without fixed toggle horizontal 4P 1 direct with long terminal shield 9 0.38 mm

600 + 300 mm Prisma G floor-standing enclosure + duct ComPact NSX630 without fixed toggle horizontal 3P 1 direct with long terminal shield 6 0.32 mm

600 + 300 mm Prisma G wall-mounted enclosure + duct ComPact NSX630 without fixed toggle horizontal 3P 1 direct with long terminal shield 6 0.32 mm

 600 ± 300 mm Prisma G floor-standing enclosure \pm duct ComPact NSX630 without fixed toggle horizontal 4P 1 direct with long terminal shield 6 0.32 mm

600 + 300 mm Prisma G wall-mounted enclosure + duct ComPact NSX630 without fixed toggle horizontal 4P 1 direct with long terminal shield 6 0.32 mm

850 mm Prisma G floor-standing enclosure ComPact NSX630 without fixed toggle horizontal 3P 1 direct with long terminal shield 9 0.38 mm

850 mm Prisma G floor-standing enclosure ComPact NSX630 without fixed toggle horizontal 4P 1 direct with long terminal shield 9 0.38 mm

850 mm Prisma G floor-standing enclosure ComPact NSX630 without fixed toggle horizontal 3P 1 direct with long terminal shield 6 0.32 mm

850 mm Prisma G floor-standing enclosure ComPact NSX630 without fixed toggle horizontal 4P 1 direct with long terminal shield 6 0.32 mm

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.900 cm
Package 1 Width	29.000 cm
Package 1 Length	47.000 cm
Package 1 Weight	2.300 kg
Unit Type Of Package 2	S04
Number Of Units In Package 2	8
Package 2 Height	30.000 cm
Package 2 Width	40.000 cm
Package 2 Length	60.000 cm
Package 2 Weight	19.050 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	96
Package 3 Height	105.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	225.840 kg

Contractual warranty

Warranty 18 months



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc
⊘	Toxic Heavy Metal Free
⊘	Mercury Free
⊘	Rohs Exemption Information Yes
Ø	Halogen Free Plastic Parts Product

Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile