



MOUNTING PLATE INF32 HZ/ INF32-40 VERTIC ROT.HANDLE

03113

! Discontinued on: 9 Aug 2023

EAN Code: 3303430031130

① Discontinued

Main

Range	Prisma
Range Of Product	Prisma G
Product Or Component Type	Mounting plate
Accessory / Separate Part Category	Installation accessory
Range Compatibility	Prisma Prisma G enclosure
Installation Description	Floor-standing enclosure - width 600 mm Wall-mounted enclosure - width 600 mm
Installed Device	FuPact: fixed INF32 - control: extended rotary handle - vertical installation FuPact: fixed INF32 - control: extended rotary handle - horizontal installation FuPact: fixed INF40 - control: extended rotary handle - vertical installation
Poles Description	4 x 3P: fixed INF32 vertical installation 1 x 3P: fixed INF32 horizontal installation 1 x 4P: fixed INF32 horizontal installation 3 x 4P: fixed INF32 vertical installation 4 x 3P: fixed INF40 vertical installation 3 x 4P: fixed INF40 vertical installation
Number Of Vertical Modules [50 Mm]	3 module(s): INF32, direct in 600 mm Widefloor-standing enclosure 3 module(s): INF32, direct in 600 mm Widewall-mounted enclosure 3 module(s): INF40, direct in 600 mm Widefloor-standing enclosure 3 module(s): INF40, direct in 600 mm Widewall-mounted enclosure
Standards	IEC 61439-2
Product Certifications	ASEFA

Complementary

Protective Treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Surface Finish	Matt Smooth
Colour	White (RAL 9001)
Width	600 mm
Height	150 mm
Net Weight	0.9 kg

Functional Unit	600 mm Prisma G floor-standing enclosure FuPact INF32 fixed extended rotary
	handle vertical 3P 4 direct 3 40 mm

600~mm Prisma G wall-mounted enclosure FuPact INF32 fixed extended rotary handle vertical 3P 4 direct 3 40 mm

600 mm Prisma G floor-standing enclosure FuPact INF32 fixed extended rotary handle horizontal 3P 1 direct 3 40 mm

600 mm Prisma G wall-mounted enclosure FuPact INF32 fixed extended rotary handle horizontal 3P 1 direct 3 40 mm

600 mm Prisma G floor-standing enclosure FuPact INF32 fixed extended rotary handle horizontal 4P 1 direct 3 40 mm

600 mm Prisma G wall-mounted enclosure FuPact INF32 fixed extended rotary handle horizontal 4P 1 direct 3 40 mm

600~mm Prisma G floor-standing enclosure FuPact INF32 fixed extended rotary handle vertical 4P 3 direct 3 40 mm

600 mm Prisma G wall-mounted enclosure FuPact INF32 fixed extended rotary handle vertical 4P 3 direct 3 40 mm

600 mm Prisma G floor-standing enclosure FuPact INF40 fixed extended rotary handle vertical 3P 4 direct 3 40 mm

600 mm Prisma G wall-mounted enclosure FuPact INF40 fixed extended rotary handle vertical 3P 4 direct 3 40 mm

600 mm Prisma G floor-standing enclosure FuPact INF40 fixed extended rotary

handle vertical 4P 3 direct 3 40 mm 600 mm Prisma G wall-mounted enclosure FuPact INF40 fixed extended rotary handle vertical 4P 3 direct 3 40 mm

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.800 cm
Package 1 Width	14.600 cm
Package 1 Length	47.000 cm
Package 1 Weight	900.000 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	20
Package 2 Height	20.000 cm
Package 2 Width	40.000 cm
Package 2 Length	60.000 cm
Package 2 Weight	18.760 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	80
Package 3 Height	45.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	75.040 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc
⊘	Toxic Heavy Metal Free
⊘	Mercury Free
⊘	Rohs Exemption Information Yes
⊘	Halogen Free Plastic Parts Product

Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile