Product datasheet

Specifications



MODULAR FRONT PLATE W850 4M

03217

() Discontinued on: 9 Aug 2023

EAN Code: 3303430032175

① Discontinued

Main

Range	Prisma	
Range Of Product	Prisma G	
Product Or Component Type	Front plate	
Accessory / Separate Part Category	Installation accessory	
Range Compatibility	Prisma Prisma G enclosure	
Type Of Front Plate	Modular	
Installed Device	Acti 9: fixed modular device Multi9: fixed modular device ComPact: fixed INS100 - control: direct front rotary handle - vertical installation ComPact: fixed INS125 - control: direct front rotary handle - vertical installation ComPact: fixed INS160 - control: direct front rotary handle - vertical installation ComPact: fixed INS40 - control: direct front rotary handle - vertical installation ComPact: fixed INS40 - control: direct front rotary handle - vertical installation ComPact: fixed INS63 - control: direct front rotary handle - vertical installation	
Poles Description	4 x 3P: modular rail support: INS100 vertical installation 4 x 4P: modular rail support: INS100 vertical installation 4 x 3P: modular rail support: INS125 vertical installation 4 x 4P: modular rail support: INS125 vertical installation 4 x 3P: modular rail support: INS160 vertical installation 4 x 4P: modular rail support: INS160 vertical installation 4 x 4P: modular rail support: INS40 vertical installation 4 x 4P: modular rail support: INS40 vertical installation 4 x 4P: modular rail support: INS40 vertical installation 4 x 4P: modular rail support: INS63 vertical installation 4 x 4P: modular rail support: INS63 vertical installation	

Complementary

Enclosure/Cubicle Description	Floor-standing enclosure - width 850 mm
Connection Position	Direct connection
9 Mm Pitches	72
Number Of 18 Mm Modules Per Row	36
Number Of Vertical Modules [50 Mm]	4
Standards	IEC 61439-1 IEC 61439-2
Product Certifications	ASEFA
Surface Finish	Matt Smooth
Protective Treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White (RAL 9001)
Height	200 mm

Width	850 mm
Net Weight	1.22 kg
Quantity Per Set	Set of 1
Functional Unit	 850 mm Prisma G floor-standing enclosure ComPact INS100 fixed direct front rotary handle vertical 3P 4 direct 4 850 mm Prisma G floor-standing enclosure ComPact INS100 fixed direct front rotary handle vertical 3P 4 direct 4 850 mm Prisma G floor-standing enclosure ComPact INS125 fixed direct front rotary handle vertical 3P 4 direct 4 850 mm Prisma G floor-standing enclosure ComPact INS125 fixed direct front rotary handle vertical 4P 4 direct 4 850 mm Prisma G floor-standing enclosure ComPact INS125 fixed direct front rotary handle vertical 3P 4 direct 4 850 mm Prisma G floor-standing enclosure ComPact INS160 fixed direct front rotary handle vertical 3P 4 direct 4 850 mm Prisma G floor-standing enclosure ComPact INS160 fixed direct front rotary handle vertical 3P 4 direct 4 850 mm Prisma G floor-standing enclosure ComPact INS160 fixed direct front rotary handle vertical 3P 4 direct 4 850 mm Prisma G floor-standing enclosure ComPact INS40 fixed direct front rotary handle vertical 3P 4 direct 4 850 mm Prisma G floor-standing enclosure ComPact INS40 fixed direct front rotary handle vertical 3P 4 direct 4 850 mm Prisma G floor-standing enclosure ComPact INS63 fixed direct front rotary handle vertical 3P 4 direct 4 850 mm Prisma G floor-standing enclosure ComPact INS63 fixed direct front rotary handle vertical 3P 4 direct 4 850 mm Prisma G floor-standing enclosure ComPact INS63 fixed direct front rotary handle vertical 3P 4 direct 4 850 mm Prisma G floor-standing enclosure ComPact INS63 fixed direct front rotary handle vertical 4P 4 direct 4 850 mm Prisma G floor-standing enclosure ComPact INS63 fixed direct front rotary handle vertical 4P 4 direct 4 850 mm Prisma G floor-standing enclosure ComPact INS63 fixed direct front rotary handle vertical 4P 4 direct 4

Environment

Ip Degree Of Protection IP30

Packing Units

-	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3 cm
Package 1 Width	20.5 cm
Package 1 Length	75 cm
Package 1 Weight	1.214 kg
Unit Type Of Package 2	CAR
Number Of Units In Package 2	6
Package 2 Height	10.5 cm
Package 2 Width	22 cm
Package 2 Length	75.5 cm
Package 2 Weight	7.61 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	192
Package 3 Height	81 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	254 kg

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
 Toxic Heavy Metal Free
 Mercury Free
 Rohs Exemption Information Yes
 Halogen Free Plastic Parts Product

Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
	Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile