Product datasheet

Specifications





FRONT PLATE VIGI CVS250 HORIZONTAL FIXED TOGGLE W600 4M

03238

! Discontinued on: 9 Aug 2023

① Discontinued

EAN Code: 3303430032380

Main

Range	Prisma	
Range Of Product	Prisma G	
Product Or Component Type	Front plate	
Accessory / Separate Part Category	Installation accessory	
Range Compatibility	Prisma Prisma G enclosure	
Type Of Front Plate	Cut-out	
Type Of Front Plate	Cut-out	
Installed Device	EasyPact: fixed CVS100160 with earth leakage protection - control: toggle - horizontal installation EasyPact: fixed CVS250 with earth leakage protection - control: toggle - horizontal installation	
Poles Description	1 x 3P: mounting plate support: CVS100160 horizontal installation 1 x 4P: mounting plate support: CVS100160 horizontal installation 1 x 3P: mounting plate support: CVS250 horizontal installation 1 x 4P: mounting plate support: CVS250 horizontal installation	
Operating Position	Horizontal	

Complementary

Enclosure/Cubicle Description	Floor-standing enclosure + duct - width 600 + 300 mm Wall-mounted enclosure + duct - width 600 + 300 mm
Connection Position	Direct connection
Number Of Vertical Modules [50 Mm]	4
Standards	IEC 61439-1 IEC 61439-2
Product Certifications	ASEFA
Surface Finish	Matt Smooth
Protective Treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White (RAL 9001)
Height	200 mm
Net Weight	0.84 kg
Quantity Per Set	Set of 1

Functional Unit 600 + 300 mm Prisma G floor-standing enclosure + duct EasyPact CVS100...160

with fixed toggle horizontal 3P 1 direct with long terminal shield 4

600 + 300 mm Prisma G wall-mounted enclosure + duct EasyPact CVS100...160 with fixed toggle horizontal 3P 1 direct with long terminal shield 4

600 + 300 mm Prisma G floor-standing enclosure + duct EasyPact CVS100...160

with fixed toggle horizontal 4P 1 direct with long terminal shield 4

600 + 300 mm Prisma G wall-mounted enclosure + duct EasyPact CVS100...160

with fixed toggle horizontal 4P 1 direct with long terminal shield 4

 $600 \pm 300 \; \text{mm}$ Prisma G floor-standing enclosure + duct EasyPact CVS250 with fixed toggle horizontal 3P 1 direct with long terminal shield 4

600 + 300 mm Prisma G wall-mounted enclosure + duct EasyPact CVS250 with fixed

toggle horizontal 3P 1 direct with long terminal shield 4

600 + 300 mm Prisma G floor-standing enclosure + duct EasyPact CVS250 with

fixed toggle horizontal 4P 1 direct with long terminal shield 4

600 + 300 mm Prisma G wall-mounted enclosure + duct EasyPact CVS250 with fixed

toggle horizontal 4P 1 direct with long terminal shield 4

Environment

Ip Degree Of Protection IP30

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	21.0 cm
Package 1 Width	51.0 cm
Package 1 Length	3.0 cm
Package 1 Weight	840.0 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	10
Package 2 Height	17.0 cm
Package 2 Width	22.5 cm
Package 2 Length	53.0 cm
Package 2 Weight	10.36 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	90
Package 3 Height	31.0 cm
Package 3 Width	80.0 cm
Package 3 Length	120.0 cm
Package 3 Weight	107.8 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc
⊘	Toxic Heavy Metal Free
⊘	Mercury Free
⊘	Rohs Exemption Information Yes
Ø	Halogen Free Plastic Parts Product

Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile