
Product datasheet

Specifications

 <u>
Green</u> <u>
Premium</u>[™]



(!) Discontinued

FRONT PLATE INS630 HORIZONTAL W600 9M

03271

() Discontinued on: 9 Aug 2023

EAN Code: 3303430032717

Main

Wall		
Range	Prisma	
Range Of Product	Prisma G	
Product Or Component Type	Front plate	
Accessory / Separate Part Category	Installation accessory	
Range Compatibility	Prisma Prisma G enclosure	
Type Of Front Plate	Cut-out	
Installed Device	ComPact: fixed INS320400 - control: direct front rotary handle - horizontal installation ComPact: fixed INS500630 - control: direct front rotary handle - horizontal installation ComPact: fixed INV320400 - control: direct front rotary handle - horizontal installation ComPact: fixed INV500630 - control: direct front rotary handle - horizontal installation	
Poles Description	1 x 3P: mounting plate support: INS320400 horizontal installation 1 x 4P: mounting plate support: INS320400 horizontal installation 1 x 3P: mounting plate support: INS500630 horizontal installation 1 x 4P: mounting plate support: INS500630 horizontal installation 1 x 3P: mounting plate support: INV320400 horizontal installation 1 x 4P: mounting plate support: INV320400 horizontal installation 1 x 3P: mounting plate support: INV320400 horizontal installation 1 x 4P: mounting plate support: INV500630 horizontal installation 1 x 4P: mounting plate support: INV500630 horizontal installation	
Operating Position	Horizontal	

Complementary

Enclosure/Cubicle Description	Floor-standing enclosure + duct - width 600 + 300 mm Wall-mounted enclosure + duct - width 600 + 300 mm
Connection Position	Direct connection
Number Of Vertical Modules [50 Mm]	6
Standards	IEC 61439-1 IEC 61439-2
Product Certifications	ASEFA
Material	Steel
Surface Finish	Smooth Matt
Protective Treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White (RAL 9001)
Height	300 mm

Width	500 mm
Net Weight	1.08 kg
Quantity Per Set	Set of 1
Functional Unit	600 + 300 mm Prisma G floor-standing enclosure + duct ComPact INS320400 fixed
	direct front rotary handle horizontal 3P 1 direct with long terminal shield 9
	600 + 300 mm Prisma G wall-mounted enclosure + duct ComPact INS320400 fixed
	direct front rotary handle horizontal 3P 1 direct with long terminal shield 9
	600 + 300 mm Prisma G floor-standing enclosure + duct ComPact INS320400 fixed
	direct front rotary handle horizontal 4P 1 direct with long terminal shield 9
	600 + 300 mm Prisma G wall-mounted enclosure + duct ComPact INS320400 fixed
	direct front rotary handle horizontal 4P 1 direct with long terminal shield 9
	600 + 300 mm Prisma G floor-standing enclosure + duct ComPact INS320400 fixed
	direct front rotary handle horizontal 3P 1 direct with long terminal shield 6
	600 + 300 mm Prisma G wall-mounted enclosure + duct ComPact INS320400 fixed
	direct front rotary handle horizontal 3P 1 direct with long terminal shield 6
	600 + 300 mm Prisma G floor-standing enclosure + duct ComPact INS320400 fixed
	direct front rotary handle horizontal 4P 1 direct with long terminal shield 6
	600 + 300 mm Prisma G wall-mounted enclosure + duct ComPact INS320400 fixed
	direct front rotary handle horizontal 4P 1 direct with long terminal shield 6
	600 + 300 mm Prisma G floor-standing enclosure + duct ComPact INS500630 fixed
	direct front rotary handle horizontal 3P 1 direct with long terminal shield 9
	600 + 300 mm Prisma G wall-mounted enclosure + duct ComPact INS500630 fixed
	direct front rotary handle horizontal 3P 1 direct with long terminal shield 9
	600 + 300 mm Prisma G floor-standing enclosure + duct ComPact INS500630 fixed
	direct front rotary handle horizontal 4P 1 direct with long terminal shield 9
	600 + 300 mm Prisma G wall-mounted enclosure + duct ComPact INS500630 fixed
	direct front rotary handle horizontal 4P 1 direct with long terminal shield 9
	600 + 300 mm Prisma G floor-standing enclosure + duct ComPact INS500630 fixed
	direct front rotary handle horizontal 3P 1 direct with long terminal shield 6
	600 + 300 mm Prisma G wall-mounted enclosure + duct ComPact INS500630 fixed
	direct front rotary handle horizontal 3P 1 direct with long terminal shield 6
	600 + 300 mm Prisma G floor-standing enclosure + duct ComPact INS500630 fixed
	direct front rotary handle horizontal 4P 1 direct with long terminal shield 6
	600 + 300 mm Prisma G wall-mounted enclosure + duct ComPact INS500630 fixed
	direct front rotary handle horizontal 4P 1 direct with long terminal shield 6
	600 + 300 mm Prisma G floor-standing enclosure + duct ComPact INV320400 fixed
	direct front rotary handle horizontal 3P 1 direct with long terminal shield 9
	600 + 300 mm Prisma G wall-mounted enclosure + duct ComPact INV320400 fixed
	direct front rotary handle horizontal 3P 1 direct with long terminal shield 9
	600 + 300 mm Prisma G floor-standing enclosure + duct ComPact INV320400 fixed
	direct front rotary handle horizontal 4P 1 direct with long terminal shield 9
	600 + 300 mm Prisma G wall-mounted enclosure + duct ComPact INV320400 fixed
	direct front rotary handle horizontal 4P 1 direct with long terminal shield 9
	600 + 300 mm Prisma G floor-standing enclosure + duct ComPact INV320400 fixed
	direct front rotary handle horizontal 3P 1 direct with long terminal shield 6
	600 + 300 mm Prisma G wall-mounted enclosure + duct ComPact INV320400 fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 6
	600 + 300 mm Prisma G floor-standing enclosure + duct ComPact INV320400 fixed
	direct front rotary handle horizontal 4P 1 direct with long terminal shield 6 600 + 300 mm Prisma G wall-mounted enclosure + duct ComPact INV320400 fixed
	direct front rotary handle horizontal 4P 1 direct with long terminal shield 6 600 + 300 mm Prisma G floor-standing enclosure + duct ComPact INV500630 fixed
	direct front rotary handle horizontal 3P 1 direct with long terminal shield 9
	600 + 300 mm Prisma G wall-mounted enclosure + duct ComPact INV500630 fixed
	direct front rotary handle horizontal 3P 1 direct with long terminal shield 9
	600 + 300 mm Prisma G floor-standing enclosure + duct ComPact INV500630 fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 9
	600 + 300 mm Prisma G wall-mounted enclosure + duct ComPact INV500630 fixed
	direct front rotary handle horizontal 4P 1 direct with long terminal shield 9
	600 + 300 mm Prisma G floor-standing enclosure + duct ComPact INV500630 fixed
	direct front rotary handle horizontal 3P 1 direct with long terminal shield 6
	600 + 300 mm Prisma G wall-mounted enclosure + duct ComPact INV500630 fixed
	direct front rotary handle horizontal 3P 1 direct with long terminal shield 6
	600 + 300 mm Prisma G floor-standing enclosure + duct ComPact INV500630 fixed
	direct front rotary handle horizontal 4P 1 direct with long terminal shield 6
	600 + 300 mm Prisma G wall-mounted enclosure + duct ComPact INV500630 fixed
	direct front rotary handle horizontal 4P 1 direct with long terminal shield 6

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.000 cm

Package 1 Width	31.000 cm
Package 1 Length	51.000 cm
Package 1 Weight	1.080 kg
Unit Type Of Package 2	CAR
Number Of Units In Package 2	10
Package 2 Height	17.000 cm
Package 2 Width	32.000 cm
Package 2 Length	53.000 cm
Package 2 Weight	11.220 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	90
Package 3 Height	48.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	100.980 kg

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
 Toxic Heavy Metal Free
 Mercury Free
 Rohs Exemption Information Yes
 Halogen Free Plastic Parts Product

Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
	Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile