Product datasheet

Specification





FRONT PLATE INS-INV 250-630 VERTICAL W300 10M

03281

! Discontinued on: 9 Aug 2023

EAN Code: 3303430032816

Main

Range	Prisma	
Range Of Product	Prisma G	
Product Or Component Type	Front plate	
Accessory / Separate Part Category	Installation accessory	
Range Compatibility	Prisma Prisma G duct	
Type Of Front Plate	Cut-out	
Installed Device	ComPact: fixed INS320400 - control: direct front rotary handle - vertical installation ComPact: fixed INS500630 - control: direct front rotary handle - vertical installation ComPact: fixed INV320400 - control: direct front rotary handle - vertical installation ComPact: fixed INV500630 - control: direct front rotary handle - vertical installation	
Poles Description	1 x 3P: mounting plate support: INS320400 vertical installation 1 x 4P: mounting plate support: INS320400 vertical installation 1 x 3P: mounting plate support: INS500630 vertical installation 1 x 4P: mounting plate support: INS500630 vertical installation 1 x 3P: mounting plate support: INV320400 vertical installation 1 x 4P: mounting plate support: INV320400 vertical installation 1 x 3P: mounting plate support: INV500630 vertical installation 1 x 4P: mounting plate support: INV500630 vertical installation	
Operating Position	Vertical	

Complementary

Enclosure/Cubicle Description	Floor-standing duct - width 300 mm Wall-mounted duct - width 300 mm
Connection Position	Direct connection
Number Of Vertical Modules [50 Mm]	10
Standards	IEC 61439-1 IEC 61439-2
Product Certifications	ASEFA
Material	Steel
Surface Finish	Matt Smooth
Protective Treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White (RAL 9001)
Height	500 mm
Width	300 mm
Net Weight	0.96 kg

19 Apr 2024 Life Is On Schneider

Quantity Per Set	Set of 1
Functional Unit	300 mm Prisma G floor-standing duct ComPact INS320400 fixed direct front rotary
	handle vertical 3P 1 direct with long terminal shield 10
	300 mm Prisma G wall-mounted duct ComPact INS320400 fixed direct front rotary
	handle vertical 3P 1 direct with long terminal shield 10
	300 mm Prisma G floor-standing duct ComPact INS320400 fixed direct front rotary
	handle vertical 4P 1 direct with long terminal shield 10
	300 mm Prisma G wall-mounted duct ComPact INS320400 fixed direct front rotary
	handle vertical 4P 1 direct with long terminal shield 10
	300 mm Prisma G floor-standing duct ComPact INS500630 fixed direct front rotary
	handle vertical 3P 1 direct with long terminal shield 12
	300 mm Prisma G wall-mounted duct ComPact INS500630 fixed direct front rotary
	handle vertical 3P 1 direct with long terminal shield 12
	300 mm Prisma G floor-standing duct ComPact INS500630 fixed direct front rotary
	handle vertical 4P 1 direct with long terminal shield 12
	300 mm Prisma G wall-mounted duct ComPact INS500630 fixed direct front rotary
	handle vertical 4P 1 direct with long terminal shield 12
	300 mm Prisma G floor-standing duct ComPact INV320400 fixed direct front rotary
	handle vertical 3P 1 direct with long terminal shield 10
	300 mm Prisma G wall-mounted duct ComPact INV320400 fixed direct front rotary
	handle vertical 3P 1 direct with long terminal shield 10
	300 mm Prisma G floor-standing duct ComPact INV320400 fixed direct front rotary
	handle vertical 4P 1 direct with long terminal shield 10
	300 mm Prisma G wall-mounted duct ComPact INV320400 fixed direct front rotary
	handle vertical 4P 1 direct with long terminal shield 10
	300 mm Prisma G floor-standing duct ComPact INV500630 fixed direct front rotary
	handle vertical 3P 1 direct with long terminal shield 12
	300 mm Prisma G wall-mounted duct ComPact INV500630 fixed direct front rotary
	handle vertical 3P 1 direct with long terminal shield 12
	300 mm Prisma G floor-standing duct ComPact INV500630 fixed direct front rotary
	handle vertical 4P 1 direct with long terminal shield 12
	300 mm Prisma G wall-mounted duct ComPact INV500630 fixed direct front rotary
	handle vertical 4P 1 direct with long terminal shield 12

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.0 cm
Package 1 Width	26.0 cm
Package 1 Length	51.0 cm
Package 1 Weight	970.0 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	10
Package 2 Height	17.0 cm
Package 2 Width	27.0 cm
Package 2 Length	53.0 cm
Package 2 Weight	9.94 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	90
Package 3 Height	42.0 cm
Package 3 Width	80.0 cm
Package 3 Length	120.0 cm
Package 3 Weight	89.46 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc
⊘	Toxic Heavy Metal Free
⊘	Mercury Free
⊘	Rohs Exemption Information Yes
⊘	Halogen Free Plastic Parts Product

Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile