



FRONT PLATE INS630 HZ W850 6M

03287

! Discontinued on: 9 Aug 2023

EAN Code: 3303430032878

(!) Discontinued

Main

Range	Prisma	
Range Of Product	Prisma G	
Product Or Component Type	Front plate	
Accessory / Separate Part Category	Installation accessory	
Range Compatibility	Prisma Prisma G enclosure	
Type Of Front Plate	Cut-out	
Installed Device	ComPact: fixed INS320400 - control: direct front rotary handle - horizontal installation ComPact: fixed INS500630 - control: direct front rotary handle - horizontal installation ComPact: fixed INV320400 - control: direct front rotary handle - horizontal installation ComPact: fixed INV500630 - control: direct front rotary handle - horizontal installation	
Poles Description	1 x 3P: mounting plate support: INS320400 horizontal installation 1 x 4P: mounting plate support: INS320400 horizontal installation 1 x 3P: mounting plate support: INS500630 horizontal installation 1 x 4P: mounting plate support: INS500630 horizontal installation 1 x 3P: mounting plate support: INV320400 horizontal installation 1 x 4P: mounting plate support: INV320400 horizontal installation 1 x 3P: mounting plate support: INV500630 horizontal installation 1 x 4P: mounting plate support: INV500630 horizontal installation	
Operating Position	Horizontal	

Complementary

Enclosure/Cubicle Description	Floor-standing enclosure - width 850 mm	
Connection Position	Connection block	
Number Of Vertical Modules [50 Mm]	6	
Standards	IEC 61439-2 IEC 61439-1	
Product Certifications	ASEFA	
Surface Finish	Matt Smooth	
Protective Treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder	
Colour	White (RAL 9001)	
Height	300 mm	
Width	850 mm	
Net Weight	1.94 kg	

Quantity Per Set	Set of 1
Functional Unit	850 mm Prisma G floor-standing enclosure ComPact INS320400 fixed direct front
	rotary handle horizontal 3P 1 direct with long terminal shield 9
	850 mm Prisma G floor-standing enclosure ComPact INS320400 fixed direct front
	rotary handle horizontal 4P 1 direct with long terminal shield 9
	850 mm Prisma G floor-standing enclosure ComPact INS320400 fixed direct front
	rotary handle horizontal 3P 1 direct with long terminal shield 6
	850 mm Prisma G floor-standing enclosure ComPact INS320400 fixed direct front
	rotary handle horizontal 4P 1 direct with long terminal shield 6
	850 mm Prisma G floor-standing enclosure ComPact INS500630 fixed direct front
	rotary handle horizontal 3P 1 direct with long terminal shield 9
	850 mm Prisma G floor-standing enclosure ComPact INS500630 fixed direct front
	rotary handle horizontal 4P 1 direct with long terminal shield 9
	850 mm Prisma G floor-standing enclosure ComPact INS500630 fixed direct front
	rotary handle horizontal 3P 1 direct with long terminal shield 6
	850 mm Prisma G floor-standing enclosure ComPact INS500630 fixed direct front
	rotary handle horizontal 4P 1 direct with long terminal shield 6
	850 mm Prisma G floor-standing enclosure ComPact INV320400 fixed direct front
	rotary handle horizontal 3P 1 direct with long terminal shield 9
	850 mm Prisma G floor-standing enclosure ComPact INV320400 fixed direct front
	rotary handle horizontal 4P 1 direct with long terminal shield 9
	850 mm Prisma G floor-standing enclosure ComPact INV320400 fixed direct front
	rotary handle horizontal 3P 1 direct with long terminal shield 6
	850 mm Prisma G floor-standing enclosure ComPact INV320400 fixed direct front
	rotary handle horizontal 4P 1 direct with long terminal shield 6
	850 mm Prisma G floor-standing enclosure ComPact INV500630 fixed direct front
	rotary handle horizontal 3P 1 direct with long terminal shield 9
	850 mm Prisma G floor-standing enclosure ComPact INV500630 fixed direct front
	rotary handle horizontal 4P 1 direct with long terminal shield 9
	850 mm Prisma G floor-standing enclosure ComPact INV500630 fixed direct front
	rotary handle horizontal 3P 1 direct with long terminal shield 6
	850 mm Prisma G floor-standing enclosure ComPact INV500630 fixed direct front
	rotary handle horizontal 4P 1 direct with long terminal shield 6

Environment

Ip Degree Of Protection	IP30		
-------------------------	------	--	--

Packing Units

r aciming critic	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3 cm
Package 1 Width	30 cm
Package 1 Length	75 cm
Package 1 Weight	1.94 kg
Unit Type Of Package 2	CAR
Number Of Units In Package 2	4
Package 2 Height	6.5 cm
Package 2 Width	31.5 cm
Package 2 Length	78 cm
Package 2 Weight	8.15 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	40
Package 3 Height	47 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	93 kg

Contractual warranty

Warranty

18 months



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc
⊘	Toxic Heavy Metal Free
⊘	Mercury Free
⊘	Rohs Exemption Information Yes
⊘	Halogen Free Plastic Parts Product

Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)	
	EU RoHS Declaration	
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)	
Environmental Disclosure	Product Environmental Profile	