



### Main

Range	Prisma
Range compatibility	Prisma P Prisma G
Product or component type	Front plate
Accessory / separate part category	Installation accessory
Type of front plate	Cut-out
Installed device	Compact : fixed NSX400 with earth leakage protection - control: toggle - vertical installation Compact : fixed NSX630 with earth leakage protection - control: toggle - vertical installation Compact : plug-in NSX400 with earth leakage protection - control: toggle - vertical installation Compact : plug-in NSX630 with earth leakage protection - control: toggle - vertical installation
Poles description	1 x 4P : mounting plate support : NSX400 vertical installation 1 x 3P : mounting plate support : NSX400 vertical installation 1 x 3P : mounting plate support : NSX630 vertical installation 1 x 4P : mounting plate support : NSX630 vertical installation
Operating position	Vertical

### Complementary

Enclosure/Cubicle description	Floor-standing duct - width 300 mm Wall-mounted duct - width 300 mm Cubicle - width 400 mm, depth 400 mm
Connection position	Front connection Direct connection
Number of vertical modules [50 mm]	9
Standards	IEC 61439-2 IEC 61439-1
Product certifications	ASEFA
Quantity per set	Set of 1
Height	500 mm
Width	250 mm
Product weight	1 kg
Material	Steel

Surface finish	Matt Smooth
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White RAL 9001

## Environment

IK degree of protection	IK07 conforming to EN/IEC 62262
-------------------------	---------------------------------

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0750 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

## Contractual warranty

Warranty period	18 months
-----------------	-----------