



Main

| | |
|------------------------------------|--|
| Range | Prisma |
| Range compatibility | Prisma P Prisma G |
| Product or component type | Front plate |
| Accessory / separate part category | Installation accessory |
| Type of front plate | Cut-out |
| Installed device | Fupact : fixed INF32 - control: extended rotary handle - vertical installation Fupact : fixed INF40 - control: extended rotary handle - vertical installation |
| Poles description | 4 x 3P : mounting plate support : INF32 vertical installation 4 x 3P : mounting plate support : INF40 vertical installation |
| Operating position | Vertical |

Complementary

| | |
|------------------------------------|--|
| Enclosure/Cubicle description | Floor-standing enclosure - width 600 mm Wall-mounted enclosure - width 600 mm Cubicle - width 650 mm, depth 400 mm |
| Number of vertical modules [50 mm] | 3 |
| Standards | IEC 61439-2 IEC 61439-1 |
| Product certifications | ASEFA |
| Quantity per set | Set of 1 |
| Height | 150 mm |
| Width | 500 mm |
| Product weight | 0.66 kg |
| Material | Steel |
| Surface finish | Matt Smooth |
| Protective treatment | Electrophoresis treatment and hot-polymerised polyester epoxy powder |
| Colour | White RAL 9001 |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

| | |
|-------------------------|---------------------------------|
| IK degree of protection | IK07 conforming to EN/IEC 62262 |
|-------------------------|---------------------------------|

Offer Sustainability

| | |
|----------------------------------|---|
| Sustainable offer status | Green Premium product |
| RoHS (date code: YYWW) | Compliant - since 0701 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity |
| REACH | Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold |
| Product environmental profile | Available |
| Product end of life instructions | Need no specific recycling operations |

Contractual warranty

| | |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|