
Product datasheet

Specifications

Sreen Premium[™]



(!) Discontinued

M. PLATE ISFT 100N

03553

- () Discontinued on: 30 Sept 2020
- (!) End-of-service on: 22 Dec 2020

EAN Code: 3303430035534

Main

Range	Prisma
Range Of Product	Prisma P
Product Or Component Type	Mounting plate
Accessory / Separate Part Category	Installation accessory
Range Compatibility	Prisma Prisma P cubicle
Installation Description	Cubicle - width 650 mm depth 400 mm
Installed Device	FuPact: fixed ISFT100N - control: fuse carriers handle - vertical installation
Poles Description	8 x 3P: fixed ISFT100N vertical installation
Number Of Vertical Modules [50 Mm]	8 module(s): ISFT100N, direct in 650 mm Widecubicle
Standards	IEC 61439-2
Product Certifications	ASEFA

Complementary

Protective Treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Surface Finish	Matt Smooth
Colour	White (RAL 9001)
Width	550 mm
Height	350 mm
Net Weight	2.22 kg
Functional Unit	650 mm 400 mm Prisma P cubicle FuPact ISFT100N fixed fuse carriers handle vertical 3P 8 direct 8 112.5 mm

Packing Units

0	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3 cm
Package 1 Width	16 cm
Package 1 Length	58 cm
Package 1 Weight	2.22 kg

Contractual warranty

Disclaimer. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes
Halogen Free Plastic Parts Product

Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information