

Product datasheet

Specifications



POWER SUPPLY BLOCK NSX/ CVS/INS-INV 630 4P

04071

! Discontinued on: 5 Apr 2023

EAN Code: 3303430040712

! Discontinued

Main

Range	Linery
Range Of Product	Linery
Product Or Component Type	Power supply block
Product Name	Linery BW
Product Name	Prisma Prisma P enclosure Prisma Prisma G enclosure Linery Linery BW busbar
Accessory / Separate Part Category	Current distribution accessory
Provided Equipment	With connection
Standards	IEC 61439-1, inside Prisma IEC 61439-2, inside Prisma
Product Certifications	ASEFA

Complementary

Cubicle-Device Connection	Linery BW busbar
Poles Description	4P
Installation Description	Cubicle - width 650 mm Floor-standing enclosure - width 850 mm Floor-standing enclosure + duct - width 600 + 300 mm Wall-mounted enclosure + duct - width 600 + 300 mm
Installed Device	ComPact: fixed NSX630 without earth leakage protection - control: toggle horizontal installation ComPact: fixed INS500...630 - control: direct front rotary handle horizontal installation ComPact: fixed INV500...630 - control: direct front rotary handle horizontal installation EasyPact: fixed CVS630 without earth leakage protection - control: toggle horizontal installation
[Ie] Rated Operational Current	630 A
[In] Rated Current	630 A
Net Weight	2.86 kg
Quantity Per Set	Set of 1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Functional Unit

[illegible]

rotary handle horizontal 4P 1 direct with long terminal shield 6
600 + 300 mm Prisma G floor-standing enclosure + duct ComPact NSX630 without
fixed toggle horizontal 3P 1 connection block 9
600 + 300 mm Prisma G wall-mounted enclosure + duct ComPact NSX630 without
fixed toggle horizontal 3P 1 connection block 9
600 + 300 mm Prisma G floor-standing enclosure + duct ComPact NSX630 without
fixed toggle horizontal 4P 1 connection block 9
600 + 300 mm Prisma G wall-mounted enclosure + duct ComPact NSX630 without
fixed toggle horizontal 4P 1 connection block 9
600 + 300 mm Prisma G floor-standing enclosure + duct ComPact NSX630 without
fixed toggle horizontal 3P 1 connection block 6
600 + 300 mm Prisma G wall-mounted enclosure + duct ComPact NSX630 without
fixed toggle horizontal 3P 1 connection block 6
600 + 300 mm Prisma G floor-standing enclosure + duct ComPact NSX630 without
fixed toggle horizontal 4P 1 connection block 6
600 + 300 mm Prisma G wall-mounted enclosure + duct ComPact NSX630 without
fixed toggle horizontal 4P 1 connection block 6
600 + 300 mm Prisma G floor-standing enclosure + duct ComPact NSX630 without
fixed toggle horizontal 3P 1 direct with long terminal shield 9
600 + 300 mm Prisma G wall-mounted enclosure + duct ComPact NSX630 without
fixed toggle horizontal 3P 1 direct with long terminal shield 9
600 + 300 mm Prisma G floor-standing enclosure + duct ComPact NSX630 without
fixed toggle horizontal 4P 1 direct with long terminal shield 9
600 + 300 mm Prisma G wall-mounted enclosure + duct ComPact NSX630 without
fixed toggle horizontal 4P 1 direct with long terminal shield 9
600 + 300 mm Prisma G floor-standing enclosure + duct ComPact NSX630 without
fixed toggle horizontal 3P 1 direct with long terminal shield 6
600 + 300 mm Prisma G wall-mounted enclosure + duct ComPact NSX630 without
fixed toggle horizontal 3P 1 direct with long terminal shield 6
600 + 300 mm Prisma G floor-standing enclosure + duct ComPact NSX630 without
fixed toggle horizontal 4P 1 direct with long terminal shield 6
600 + 300 mm Prisma G wall-mounted enclosure + duct ComPact NSX630 without
fixed toggle horizontal 4P 1 direct with long terminal shield 6

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	12.5 cm
Package 1 Width	19.0 cm
Package 1 Length	24.8 cm
Package 1 Weight	2.87 kg
Unit Type Of Package 2	P12
Number Of Units In Package 2	72
Package 2 Height	65.0 cm
Package 2 Width	80.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	218.64 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes

Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile