## **Product datasheet**

Specifications





# Ethernet fibre converter SM/LC 2CH - 100 MB

Local distributor code: 400938536

140NRP31201

EAN Code: 3595864179254

! To be discontinu

### Main

Range Of Product	Modicon Quantum automation platform	
Product Or Component Type	Fibre converter	
Optic Fiber Type	Single mode	

### Complementary

<b>Bus Current Requirement</b>	1000 mA	
Power Dissipation In W	5 W	
Inrush Current	1 A at 5 V DC	
Number Of Port	2 fiber optic, connector type: LC 2 ETHERNET, connector type: RJ45	
Local Signalling	1 LED green with RDY marking for module status 1 LED red with ERR marking for internal fault, module failure 1 LED green with STS1 marking for channel 1 link status 1 LED green with FX1 ACT marking for channel 1 communication status 1 LED green with STS2 marking for channel 2 link status 1 LED green with FX2 ACT marking for channel 2 communication status	
Wavelength	1310 nm	
Optic Distance Between 2 Transceivers	15000 m (9/125 μm), optical power: -158 dBm	
Attenuation	-158 dB (9/125 μm)	
Rise/Fall Time	2.5 ns	
Receiver Sensitivity	- 28 dBm	
Detected Silence	-45 dBm	
Marking	CE	
Material	PC (polycarbonate)	
Width	40.34 mm	
Height	250 mm	
Depth	103.85 mm	
Net Weight	0.554 kg	

### **Environment**

Ambient Air Temperature For Operation	060 °C
Ambient Air Temperature For Storage	-4085 °C
Relative Humidity	095 %

Operating Altitude	02000 m
Standards	UL 508 CSA C22.2 No 142 FM Class 1 Division 2
Product Certifications	TÜV Merchant Navy C-Tick

### **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	16.3 cm
Package 1 Width	4.5 cm
Package 1 Length	31.2 cm
Package 1 Weight	614.0 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	7
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	4.298 kg

### **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

### Well-being performance

<b>②</b>	Reach Free Of Svhc	
<b>Ø</b>	Mercury Free	
<b>Ø</b>	Rohs Exemption Information	Yes


### **Certifications & Standards**

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information

### **Dimensions Drawings**

### **Racks for Modules Mounting**

#### **Dimensions of Modules and Racks**



- (1) 2 slots
- (2) 3 slots
- (3) 4 slots
- (4) 6 slots
- (5) 10 slots
- (6) 16 slots