



15005 has not been replaced. Please contact your customer care centre for more information.

Main

| | |
|---------------------------|---------|
| Product or component type | Switch |
| Device short name | I |
| Device application | Control |
| Poles description | 1P |
| Utilisation category | AC-22A |
| Suitability for isolation | Yes |

Complementary

| | |
|--|---|
| [Ie] rated operational current | 20 A at 250 V AC 50/60 Hz |
| [Ue] rated operational voltage | 250 V AC 50/60 Hz |
| [Ui] rated insulation voltage | AC 50/60 Hz conforming to EN/IEC 60669-2-4 |
| [Uimp] rated impulse withstand voltage | 4 kV |
| Control type | Toggle |
| Local signalling | ON/OFF indication |
| Contact position indicator | Yes |
| Mounting mode | Fixed |
| Mounting support | DIN rail |
| 9 mm pitches | 2 |
| Colour | Grey |
| Mechanical durability | 300000 cycles |
| Electrical durability | 30000 cycles |
| Connections - terminals | Tunnel type terminals - 1 x 1.5...1 x 10 mm ² - flexible Tunnel type terminals - 1 x 1.5...1 x 10 mm ² - rigid Tunnel type terminals - 2 x 2.5 mm ² - flexible Tunnel type terminals - 2 x 2.5 mm ² - rigid Tunnel type terminals - 2 x 4 mm ² - flexible Tunnel type terminals - 2 x 4 mm ² - rigid |
| Wire stripping length | 9 mm |
| Tightening torque | 3.5 N.m |

Environment

| | |
|-------------------------|------------------|
| Standards | EN/IEC 60669-2-4 |
| IP degree of protection | IP4 |

| | |
|------------------|---|
| Pollution degree | 2 |
| Tropicalisation | 2 |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|
