



ⓘ Discontinued

15009 has not been replaced. Please contact your customer care centre for more information.

### Main

Product or component type	Switch
Device short name	I
Device application	Control
Poles description	1P
Utilisation category	AC-22A
Suitability for isolation	Yes

### Complementary

[Ie] rated operational current	32 A at 250 V AC 50/60 Hz
[Ue] rated operational voltage	250 V AC 50/60 Hz
[Ui] rated insulation voltage	AC 50/60 Hz conforming to EN/IEC 60669-2-4
[Uimp] rated impulse withstand voltage	4 kV
Control type	Toggle
Local signalling	ON/OFF indication
Contact position indicator	Yes
Mounting mode	Fixed
Mounting support	DIN rail
9 mm pitches	2
Colour	Grey
Mechanical durability	300000 cycles
Electrical durability	30000 cycles
Connections - terminals	Tunnel type terminals - 1 x 1.5...1 x 10 mm <sup>2</sup> - flexible Tunnel type terminals - 1 x 1.5...1 x 10 mm <sup>2</sup> - rigid Tunnel type terminals - 2 x 2.5 mm <sup>2</sup> - flexible Tunnel type terminals - 2 x 2.5 mm <sup>2</sup> - rigid Tunnel type terminals - 2 x 4 mm <sup>2</sup> - flexible Tunnel type terminals - 2 x 4 mm <sup>2</sup> - rigid
Wire stripping length	9 mm
Tightening torque	3.5 N.m

### Environment

Standards	EN/IEC 60669-2-4
IP degree of protection	IP4

---

Pollution degree	2
Tropicalisation	2

---

### Contractual warranty

---

Warranty	18 months
----------	-----------

---