



Main

Range of product	Thorsman
Product or component type	Anchor
Mounting support	Brick Rock Concrete Stone
Drilling diameter	14 mm
Minimum drilling depth	60 mm
Thread type	M8
Threaded length	55 mm
Practical load capacity	4 kN pull-out load concrete
Material	Steel

Complementary

Surface finish	Zinc plated
----------------	-------------

Environment

Quantity per set	Set of 100
Sale per indivisible quantity	100

Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
-------------------	---

Contractual warranty

Warranty	18 months
----------	-----------