



### Main

Range of product	Multi 9
Product name	Multi 9 CM
Product or component type	Selector switch
Device short name	CMD
Device application	Electrical circuit control
Contacts type and composition	1 C/O
[Ue] rated operational voltage	415 V AC 50/60 Hz
Standards	UL VDE 0660 part 107 EN 60947-3 IEC 60947-3

### Complementary

[Ie] rated operational current	10 A
Control type	Rotary handle 5 positions
Marking	0 - 1 - 2 - 3 - 4
Mounting support	DIN rail
9 mm pitches	4
Height	60 mm
Width	36 mm
Depth	75 mm
Colour	Grey
Mechanical durability	1000000 cycles
Electrical durability	AC-21A: 200000 cycles
Connections - terminals	Jumper terminals 1.5 mm <sup>2</sup>
Wire stripping length	9 mm for downside connection
Tightening torque	1 N.m downside

### Environment

Ambient air temperature for operation	-20...55 °C
Ambient air temperature for storage	-25...80 °C

Contractual warranty

---

Warranty	18 months
----------	-----------

---