

Product datasheet

Specifications



2 positions selector switch CMC - 10 A

15123

⚠ Discontinued on: 26 Apr 2019

EAN Code: 3303430151234

⚠ Discontinued

Main

Range Of Product	Multi9
Product Name	Multi9 CM
Product Or Component Type	Selector switch
Device Short Name	CMC
Device Application	Electrical circuit control
Contacts Type And Composition	1 NO + 1 NC
[Ue] Rated Operational Voltage	415 V AC 50/60 Hz
Standards	IEC 60947-3 VDE 0660 part 107 EN 60947-3 UL

Complementary

[Ie] Rated Operational Current	10 A
Control Type	Rotary handle 2 positions
Marking	1 - 2
9 Mm Pitches	4
Height	60 mm
Width	36 mm
Depth	72 mm
Colour	Grey
Mechanical Durability	1000000 cycles
Electrical Durability	AC-21A: 200000 cycles
Connections - Terminals	Jumper terminals1.5 mm²
Wire Stripping Length	9 mm for downside connection
Tightening Torque	1 N.m downside

Environment

Ambient Air Temperature For Operation	-20...55 °C
Ambient Air Temperature For Storage	-25...80 °C

Packing Units

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4 cm
Package 1 Width	7.5 cm
Package 1 Length	8 cm
Package 1 Weight	0.09 kg

Contractual warranty

Warranty	18 months
----------	-----------