



### Main

Range of product	Acti 9
Range	Acti 9
Product name	Acti 9 iCM
Product or component type	Selector switch
Device short name	ICMV
Device application	Voltmeter selector
[Ue] rated operational voltage	< 440 V AC 50/60 Hz

### Complementary

[I <sub>th</sub> ] conventional free air thermal current	10 A
[I <sub>e</sub> ] rated operational current	10 A
Control type	Rotary handle 7 positions
Marking	L3L1 - L2L3 - L1L2 - 0 - L1N - L2N - L3N
Mounting mode	Clip-on
Mounting support	DIN rail
9 mm pitches	4
Height	60 mm
Width	36 mm
Depth	75 mm
Mechanical durability	2000000 cycles
Electrical durability	1000000 cycles
Connections - terminals	Captive screw-jumper terminals - <= 1.5 mm <sup>2</sup>

### Environment

Standards	IEC 60947-3
IP degree of protection	Front face: IP66 Terminals: IP20
Ambient air temperature for operation	-20...55 °C
Ambient air temperature for storage	-25...80 °C

**Offer Sustainability**

EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
China RoHS Regulation	<a href="#">Download RoHS China Declaration</a> Product out of China RoHS scope. Substance declaration for your information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

**Contractual warranty**

Warranty	18 months
----------	-----------