

15215 has not been replaced. Please contact your customer care centre for more information.



ⓘ Discontinued

### Main

Product or component type	Transformer
Device short name	TR
Transformer type	Bell transformer

### Complementary

[Ue] rated operational voltage	230 V AC 50/60 Hz
Output voltage	12/24 V: +/- 15 % on load 16/32 V: off load
Output short-circuit protection	Built-in
Rated power in VA	25 VA
Mounting mode	Fixed
Mounting support	35 mm symmetrical DIN rail
9 mm pitches	6
Height	89 mm
Width	54 mm
Depth	60 mm
Auxiliary connection terminal	Tunnel type terminals 4 mm <sup>2</sup>

### Environment

Standards	EN 60742 IEC 61558-2-6 EN 61558-2-6
Product certifications	NF
Oversvoltage category	Class II with terminal shields in option
Ambient air temperature for operation	-20...55 °C
Ambient air temperature for storage	-25...80 °C

### Contractual warranty

Warranty	18 months
----------	-----------