


Product datasheet

Specifications



modular safety transformer - 230 V
50..60 Hz - output 12..24 V - 63 VA

15222

 **Discontinued on:** 16 Oct 2019

EAN Code: 3303430152224

 **Discontinued**

Main

Transformer Type	Safety transformer
Range Of Product	TR
Product Or Component Type	Transformer
Device Short Name	TR

Complementary

[Ue] Rated Operational Voltage	230 V AC 50/60 Hz
Output Voltage	12/24 V: +/-5 % on load 14/28 V: off load
Output Short-Circuit Protection	Built-in
Rated Power In Va	63 VA
Mounting Mode	Fixed
Mounting Support	35 mm symmetrical DIN rail
9 Mm Pitches	10
Height	89 mm
Width	90 mm
Depth	60 mm
Auxiliary Connection Terminal	Tunnel type terminals 4 mm ²

Environment

Standards	IEC 61558-2-6 EN 61558-2-6 EN 60742
Product Certifications	NF
Overvoltage Category	Class II with terminal shields in option
Ambient Air Temperature For Operation	-20...55 °C
Ambient Air Temperature For Storage	-25...80 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.8 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Width	8.5 cm
Package 1 Length	9.5 cm
Package 1 Weight	1.309 kg

Contractual warranty

Warranty	18 months
----------	-----------