# **Product datasheet**

Specifications





# Acti 9 - IH - mechanical time switch - 24 h - 100 h memory

Local distributor code: 22391881

15336

EAN Code: 3303430153368

#### Main

Range Of Product	Acti9
Product Name	Acti9 IH
Device Short Name	ІН
Product Or Component Type	Mechanical time switch
Number Of Channels	1
Function Available	Manual time changeover

## Complementary

Complementary	
Device Application	Building
Load Type	Parallel-corrected fluorescent tube 5 x 58 W 4.7 µF Parallel-corrected fluorescent tube 7 x 40 W 7 µF Parallel-corrected fluorescent tube 2 x 100 W 18 µF 230 V AC halogen lamp 1000 W 230 V AC incandescent lamp 1000 W Fluocompact lamp 700 VA Compact fluorescent lamp 150 W LED lamp < 2 W 30 W LED lamp > 2 W 300 W
Cycle Duration	24 h
Maximum Number Of Switchings	48 on - 48 off
Minimum Interval Duration	15 min
Type Of Setting	Manual time changeover
Measurement Accuracy	+/- 1 s/day 20 °C
Power Consumption In W	0.5 W
Maximum Switching Current	16 A - 250 V AC pf = 1 4 A - 250 V AC pf = 0.6
[Ue] Rated Operational Voltage	230240 V AC at 5060 Hz
Battery Life	10 year(s)
Backup Time	150 h time and program saving
Mounting Support	DIN rail
9 Mm Pitches	2
Colour Tint	White (RAL 9003)
Connections - Terminals	Screw terminals
Width	18 mm
Height	90 mm
Depth	66 mm

Net Weight	0.101 kg
Environment	
Ambient Air Temperature For Operation	-1050 °C
Ip Degree Of Protection	Terminals: IP20 B
Packing Units	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.400 cm
Package 1 Width	6.800 cm
Package 1 Length	10.000 cm
Package 1 Weight	87.000 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	100
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	9.350 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	1600
Package 3 Height	75.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	146.192 kg

## **Contractual warranty**

Warranty

18 months

## Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Mercury Free

Rohs Exemption Information Yes

### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information