



### Main

Range of product	Acti 9
Product name	Acti 9 IH
Device short name	IH
Product or component type	Mechanical time switch
Number of channels	2
Function available	Manual time changeover

### Complementary

Device application	Building
Load type	1 parallel-corrected fluorescent tube conventional ballast (58 W) 10 non-corrected fluorescent tube conventional ballast (58 W) 10 serial-corrected fluorescent tube conventional ballast (58 W) 15 non-corrected fluorescent tube conventional ballast (40 W) 15 serial-corrected fluorescent tube conventional ballast (40 W) 2 parallel-corrected fluorescent tube conventional ballast (40 W) 230 V AC halogen lamp (1100 W) 230 V AC incandescent lamp (1100 W) 3 dual mounted fluorescent tube conventional ballast (2 x 100 W) 5 dual mounted fluorescent tube conventional ballast (2 x 58 W) 6 non-corrected fluorescent tube conventional ballast (100 W) 6 serial-corrected fluorescent tube conventional ballast (100 W)
Cycle duration	24 h
Measurement accuracy	+/- 1 s/day
Maximum number of switchings	24 on - 24 off
Minimum interval duration	30 min
Type of setting	Manual time changeover
Measurement accuracy	+/- 1 s/day 20 °C
Power consumption in VA	2.5 VA
Maximum switching current	16 A - 250 V AC pf = 1 4 A - 250 V AC pf = 0.6
[Ue] rated operational voltage	230 V AC - 15...10 % at 50/60 Hz
Battery life	6 year(s)
Backup time	150 h time and program saving
Mounting support	DIN rail
9 mm pitches	6

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Colour tint	White (RAL 9003)
Connections - terminals	Screw terminals
IP degree of protection	IP20 B
Width	54 mm
Height	82 mm
Depth	66 mm
Net weight	0.216 kg

## Environment

Ambient air temperature for operation	-20...55 °C
IP degree of protection	Terminals: IP20 B

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">Download RoHS China Declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End of Life Information</a>

## Contractual warranty

Warranty	18 months
----------	-----------