

Product datasheet

Specifications



Multi 9 - IH - mechanical switch - 60 min - without memory

15338

⚠ Discontinued on: 31 Dec 2016

⚠ End-of-service on: 1 Jul 2021

⚠ Discontinued

EAN Code: 3303430153382

Main

Range Of Product	Multi9
Product Name	Multi9 IH
Device Short Name	IH
Product Or Component Type	Mechanical switch
Number Of Channels	1
Function Available	Manual time changeover

Complementary

Device Application	Building
Load Type	Parallel-corrected fluorescent tube 1 x conventional ballast 58 W Non-corrected fluorescent tube 10 x conventional ballast 58 W Serial-corrected fluorescent tube 10 x conventional ballast 58 W Non-corrected fluorescent tube 15 x conventional ballast 40 W Serial-corrected fluorescent tube 15 x conventional ballast 40 W Parallel-corrected fluorescent tube 2 x conventional ballast 40 W 230 V AC halogen lamp 1100 W 230 V AC incandescent lamp 1100 W Dual mounted fluorescent tube 3 x conventional ballast 2 x 100 W Dual mounted fluorescent tube 5 x conventional ballast 2 x 58 W Non-corrected fluorescent tube 6 x conventional ballast 100 W Serial-corrected fluorescent tube 6 x conventional ballast 100 W
Cycle Duration	60 min
Maximum Number Of Switchings	24 on - 24 off
Minimum Interval Duration	1 min 15 s
Type Of Setting	Manual time changeover
Measurement Accuracy	+/- 1 s/day
Power Consumption In Va	1 VA
Maximum Switching Current	16 A - 250 V AC pf = 1 4 A - 250 V AC pf = 0.6
[Ue] Rated Operational Voltage	230 V AC +/- 10 % at 50 Hz
Mounting Support	DIN rail
9 Mm Pitches	6
Colour Tint	White (RAL 9003)
Width	54 mm
Net Weight	0.184 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

Ambient Air Temperature For Operation	-10...50 °C
Ip Degree Of Protection	Terminals: IP20 B

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.5 cm
Package 1 Width	7.5 cm
Package 1 Length	10.8 cm
Package 1 Weight	0.184 kg

Contractual warranty

Warranty	18 months
----------	-----------