

15540 has not been replaced. Please contact your customer care centre for more information.



⚠ Discontinued

Main

Range of product	Multi 9
Product name	Multi 9 ERL
Product or component type	Extension for changeover relay
Device short name	ERL
Device application	Extension for changeover relay
Signal contacts composition	1 C/O + 1 NO
[Uc] control circuit voltage	48 V AC 50/60 Hz

Complementary

[Ie] rated operational current	10 A at 230 V AC (cos Phi = 1)
[Ui] rated insulation voltage	AC
Supply holding power	8 VA
Supply inrush power	8 VA
Mounting mode	Fixed
Mounting support	35 mm symmetrical DIN rail
9 mm pitches	2
Electrical durability	AC-21: 100000 cycles
Connections - terminals	Tunnel type terminals 0.5...6 mm ² Connection by clip

Environment

Standards	NF C 45-250 IEC 255
-----------	------------------------

Contractual warranty

Warranty	18 months
----------	-----------