Product datasheet

Specifications





motor-mechanism - MCH - 24..30 V DC

33185

EAN Code: 3303430331858

Main

Range Of Product	MasterPact NT
Range	MasterPacT
Device Short Name	gear motor MCH
Product Or Component Type	Motor mechanism
Device Application	Automatic spring charging
Range Compatibility	Masterpact MasterPact NT circuit breaker
[Uc] Control Circuit Voltage	2430 V DC

Complementary

Control Type	Motor mechanism
Maximum Charging Time	3 s
Maximum Power Consumption In Va	180 VA
Accessory / Separate Part Category	Spare parts for MasterPact NT

Packing Units

U	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.5 cm
Package 1 Width	13 cm
Package 1 Length	18 cm
Package 1 Weight	815 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	16
Package 2 Height	30 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	13.527 kg

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information