



### Main

|                           |                |
|---------------------------|----------------|
| Range of product          | Harmony 9001SK |
| Product or component type | Push-button    |
| Device short name         | 9001SK         |

### Complementary

|                       |                  |
|-----------------------|------------------|
| Bezel material        | Plastic          |
| Mounting diameter     | 30 mm            |
| Contact operation     | Standard         |
| Mechanical durability | 5000000 cycles   |
| Device presentation   | Complete product |

### Environment

|                           |  |
|---------------------------|--|
| Standards                 | EN/IEC 60947-1<br>JIS C 852<br>EN/IEC 60947-5-1<br>JIS C 4520<br>EN/IEC 60947-5-4<br>UL 508<br>CSA C22.2 No 14 |
| IP degree of protection   | IP66   |
| NEMA degree of protection | NEMA 1/2/3/3R/4/4X/6/12/13   |

### Offer Sustainability

|                            |  |
|----------------------------|--|
| Sustainable offer status   | Green Premium product  |
| REACH Regulation           | <a href="#">REACH Declaration</a>  |
| REACH free of SVHC         | Yes  |
| EU RoHS Directive          | Pro-active compliance (Product out of EU RoHS legal scope)<br><a href="#">EU RoHS Declaration</a>                    |
| Toxic heavy metal free     | Yes  |
| Mercury free               | Yes  |
| RoHS exemption information | <a href="#">Yes</a>  |
| China RoHS Regulation      | <a href="#">Download RoHS China Declaration</a><br>Pro-active China RoHS declaration (out of China RoHS legal scope) |

|                          |   |
|--------------------------|---|
| Environmental Disclosure | <a href="#">Product Environmental Profile</a>   |
| Circularity Profile      | No need of specific recycling operations  |
| WEEE                     | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |

### Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|