

Product datasheet

Specifications




Acti9 modular bell transformer iTR - 230 V 50..60 Hz - output 8 V - 4 VA

Local distributor code:

399362116

A9A15214

 **Discontinued on:** 15 Feb 2021

EAN Code: 3606480097867

 **Discontinued**

Main

Range Of Product	Acti9
Product Name	Acti9 iTR
Product Or Component Type	Transformer
Device Short Name	iTR
Transformer Type	Bell transformer

Complementary

[Ue] Rated Operational Voltage	230 V AC 50/60 Hz
Output Voltage	12 V: off load 8 V: +/- 15 % on load
Output Short-Circuit Protection	Built-in
Rated Power In Va	4 VA
Mounting Mode	Fixed
Mounting Support	35 mm symmetrical DIN rail
9 Mm Pitches	4
Height	89 mm
Width	36 mm
Depth	60 mm
Colour	White
Auxiliary Connection Terminal	Tunnel type terminalsrigid 2.5 mm² Tunnel type terminalsflexible 2.5 mm² Tunnel type terminalsflexible with ferrule 2.5 mm²
Wire Stripping Length	6 mm
Tightening Torque	0.5 N.m

Environment

Standards	EN 61558-2-6 IEC 61558-2-6 EN 60742
Product Certifications	NF
Ip Degree Of Protection	IP20 conforming to IEC 60529
Overvoltage Category	Class II with terminal shields in option
Ambient Air Temperature For Operation	-20...55 °C

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ambient Air Temperature For Storage	-25...80 °C
-------------------------------------	-------------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4 cm
Package 1 Width	7 cm
Package 1 Length	9.5 cm
Package 1 Weight	232 g

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Sustainable Packaging

Resource performance

✓ Sustainable Packaging

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Reach Regulation	REACH Declaration
------------------	-----------------------------------

Eu Rohs Directive	Compliant EU RoHS Declaration
-------------------	--

China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
-----------------------	---

Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
------	---