Product datasheet





iDPN - circuit breaker - 1P+N -20A - B curve

Local distributor code: 399366219

A9N17520

! Discontinued on: 14 Dec 2021

① Discontinued

EAN Code: 3606480530593

Main

Range Of Product	Clario
Range	Clario
Product Name	IDPN
Product Or Component Type	Miniature circuit-breaker
Device Short Name	iDPN N
Device Application	Distribution
Poles Description	1P + N
Number Of Protected Poles	1
Neutral Position	Left
[In] Rated Current	20 A
Network Type	AC
Trip Unit Technology	Thermal-magnetic
Curve Code	В
Breaking Capacity	6000 A Icn at 230 V AC 50/60 Hz conforming to EN/IEC 60898-1
Suitability For Isolation	Yes

Complementary

Network Frequency	50/60 Hz
[Ue] Rated Operational Voltage	230 V AC 50/60 Hz between phase and neutral
Magnetic Tripping Limit	35 x ln
[Ics] Rated Service Breaking Capacity	6000 A 100 % x Icn at 230 V AC 50/60 Hz conforming to EN/IEC 60898-1
Limitation Class	3 conforming to EN/IEC 60898-1
[Ui] Rated Insulation Voltage	400 V AC 50/60 Hz conforming to IEC 60947-2
[Uimp] Rated Impulse Withstand Voltage	4 kV conforming to IEC 60947-2
Contact Position Indicator	Yes
Control Type	Toggle
Local Signalling	ON/OFF indication
Mounting Mode	Clip-on
Mounting Support	DIN rail
9 Mm Pitches	2

Height	81 mm
Width	18 mm
Depth	78 mm
Net Weight	115 g
Colour	White
Mechanical Durability	20000 cycles
Electrical Durability	20000 cycles
Locking Options Description	Padlocking device
Connections - Terminals	Tunnel type terminals downstream 0.3310 mm² flexible Tunnel type terminals downstream 0.7516 mm² rigid Tunnel type terminals upstream 0.3310 mm² flexible Tunnel type terminals upstream 0.7516 mm² rigid
Wire Stripping Length	13 mm
Tightening Torque	2 N.m
Earth-Leakage Protection	Separate block

Environment

Standards	EN/IEC 60898-1
Ip Degree Of Protection	IP20 conforming to IEC 60529
Pollution Degree	3 conforming to IEC 60947-1
Tropicalisation	2 conforming to IEC 60068-1
Relative Humidity	95 % at 55 °C
Operating Altitude	2000 m
Ambient Air Temperature For Operation	-2570 °C
Ambient Air Temperature For Storage	-4070 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2 cm
Package 1 Width	7.5 cm
Package 1 Length	8.5 cm
Package 1 Weight	 119 g

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
	Product out of China RoHS scope. Substance declaration for your information
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins