


Product datasheet

Specifications

Acti9 - comb busbar - 1L+N with Aux - 9 mm pitch - 56 modules - 63A



A9N21035

 **Discontinued on:** 10 Nov 2021

EAN Code: 3606480504730

 **Discontinued**

Main

Range	Acti9
Product Or Component Type	Comb busbar
Mounting Mode	Horizontal
Accessory / Separate Part Category	Connection accessory
Lines Description	1L + N
Length In 18 Mm Modules	56

Complementary

Number Of Ways	37 ways Aux + N + 1 L
Poles Configuration For 1 Way	1 x 1P + N
Connection Pitch	9 mm between phase and neutral
Connector Type	Tooth
Distance Between Way	27 mm
Marking	N L
Insulation	Insulated
Device Presentation	Cuttable
[Ie] Rated Operational Current	63 A at 40 °C
[Ue] Rated Operational Voltage	230 V AC Ph/N
[Ui] Rated Insulation Voltage	500 V AC conforming to IEC 61439-2
Mounting Location	Top on tunnel type terminals
9 Mm Pitches	112
Width	1000 mm
Colour	Light grey (RAL 7035)
Range Compatibility	Acti 9 Acti9 C40 Acti 9 Acti9 C40 Vig Acti 9 Acti9 DT40 Acti 9 Acti9 DT40 Vig Acti 9 Acti9 iDPN Acti 9 Acti9 iDPN Vig Acti 9 Acti9 ID C40 Acti 9 Acti9 IDc Acti 9 Acti9 ITG40 Multi9 Multi9 N40

Environment

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	IEC 60947-7-1 IEC 61439-2
Fire Resistance	960 °C (30 s) conforming to IEC 60695-2-1
Pollution Degree	3 conforming to IEC 60947-7-1
Ip Degree Of Protection	IP20 with end-pieces and tooth covers

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.000 cm
Package 1 Width	12.000 cm
Package 1 Length	101.000 cm
Package 1 Weight	595.000 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	5
Package 2 Height	6.000 cm
Package 2 Width	101.000 cm
Package 2 Length	12.000 cm
Package 2 Weight	2.978 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	80
Package 3 Height	75.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	59.648 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability





Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

	Reach Free Of Svhc	
	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	Yes
<hr/>		
Reach Regulation		REACH Declaration
<hr/>		
Eu Rohs Directive		Compliant EU RoHS Declaration
<hr/>		
China Rohs Regulation		China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
<hr/>		
Weee		The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
<hr/>		