Product datasheet

Specifications





switch Acti9 iSW with indicator - 1 pole - 32 A - 250V

Local distributor code: 399367865

9367865 A9S61132

EAN Code: 3606480088933

Main

| Range | Acti9 |
|---------------------------|---------------------|
| Product Name | Acti9 iSW |
| Product Or Component Type | Switch disconnector |
| Device Short Name | iSW |
| Device Application | Control |
| Poles Description | 1P |
| Utilisation Category | AC-22A |

Complementary

| [le] Rated Operational Current | 32 A at 250 V AC 50/60 Hz |
|--|---|
| [Ue] Rated Operational Voltage | 250 V AC 50/60 Hz |
| [Ui] Rated Insulation Voltage | 250 V AC 50/60 Hz conforming to IEC EN 60669-1 |
| [Uimp] Rated Impulse Withstand Voltage | 4 kV |
| Control Type | Toggle |
| Local Signalling | ON/OFF indication and lamp |
| Signalling Circuit Voltage | AC: 230 V 50/60 Hz |
| Mounting Mode | Fixed |
| Mounting Support | DIN rail |
| 9 Mm Pitches | 2 |
| Height | 77 mm |
| Width | 18 mm |
| Depth | 70 mm |
| Colour | White |
| Mechanical Durability | 300000 cycles |
| Electrical Durability | 30000 cycles |
| Connections - Terminals | Tunnel type terminals - 10 mm² - rigid Tunnel type terminals - 10 mm² - flexible Tunnel type terminals - 10 mm² - flexible with ferrule |
| Wire Stripping Length | 9 mm |
| Tightening Torque | 1.2 N.m |

Environment

| Standards | IEC EN 60669-1 |
|---------------------------------------|----------------|
| Ip Degree Of Protection | IP4 |
| Pollution Degree | 2 |
| Tropicalisation | 2 |
| Relative Humidity | 95 % at 55 °C |
| Ambient Air Temperature For Operation | -2050 °C |
| Ambient Air Temperature For Storage | -4070 °C |

Packing Units

| _ | |
|------------------------------|----------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 2.0 cm |
| Package 1 Width | 6.5 cm |
| Package 1 Length | 8.0 cm |
| Package 1 Weight | 60.0 g |
| Unit Type Of Package 2 | BB1 |
| Number Of Units In Package 2 | 12 |
| Package 2 Height | 8.0 cm |
| Package 2 Width | 9.5 cm |
| Package 2 Length | 23.0 cm |
| Package 2 Weight | 775.0 g |
| Unit Type Of Package 3 | S03 |
| Number Of Units In Package 3 | 144 |
| Package 3 Height | 30.0 cm |
| Package 3 Width | 30.0 cm |
| Package 3 Length | 40.0 cm |
| Package 3 Weight | 9.787 kg |

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

| ⊘ | Reach Free Of Svhc | |
|----------|----------------------------|-----|
| 9 | Toxic Heavy Metal Free | |
| ② | Mercury Free | |
| ⊘ | Rohs Exemption Information | Yes |

Certifications & Standards

| Reach Regulation | REACh Declaration |
|--------------------------|---|
| Eu Rohs Directive | Compliant EU RoHS Declaration |
| China Rohs Regulation | China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure | Product Environmental Profile |
| Weee | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |
| Circularity Profile | End of Life Information |