

Product datasheet

Specifications



connecting cable - Advantys Telefast - 1.5m - 32 O 100 mA - for Allen Bradley

ABFH40H151

⚠ Discontinued on: 24 Jul 2020

⚠ Discontinued

EAN Code: 3389110705461

Main

Accessory / Separate Part Destination	Allen Bradley PLC
Range Of Product	Advantys Telefast
Accessory / Separate Part Category	Connection accessories
Accessory / Separate Part Type	Connection cable
Accessory / Separate Part Designation	Connecting cable
Number Of Channels	16

Complementary

Product Compatibility	SLC500
Cable Length	1.5 m
Type Of Signal	100 mA 32 channel output
Electrical Connection	1 connector HE10, 40 ways for PLC side 2 connectors HE10, 20 ways for Telefast end
Awg Gauge	AWG 22
Wire Section	0.324 mm ²

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.5 cm
Package 1 Width	24 cm
Package 1 Length	28 cm
Package 1 Weight	475 g

Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes
Reach Regulation		REACH Declaration
Eu Rohs Directive		Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation		China RoHS declaration