# **Product datasheet**





# Cableline 40 - installation trunking - 145Wx40 mm - 3 m

Local distributor code:

21241589

EAN Code: 3606480487132

#### Main

| Range Of Product          | Mita                  |
|---------------------------|-----------------------|
| Product Name              | Cableline 40          |
| Product Or Component Type | Installation trunking |
| Colour Tint               | White/grey            |
| Quantity Per Set          | Set of 2              |

### Complementary

| Compartment Partitioning     | 3 compartments                                 |  |
|------------------------------|--|--|
| Trunking Dimension           | 145W x 40 mm                                   |  |
| Trunking Material            | Plastic  |  |
| Front Opening Size           | 87 mm  |  |
| Device Composition           | white trunking base grey lid (x 3)             |  |
| Fixing Mode                  | Screw-fixed                                    |  |
| Material With Surface Finish | Finish UPVC (unplasticized polyvinyl chloride) |  |
| Product Compatibility        | npatibility x 25 mm mounting boxes             |  |
| Length                       | 3000 mm  |  |
| Height                       | 145 mm   |  |
| Width                        | 40 mm  |  |

#### **Environment**

| Standards                                | ANSI/TIA/EIA-568-B<br>BS 4678-4<br>BS 6701 |
|--|--|
|  | BS 7671                                    |
|  | BS EN 50173                                |
|  | BS EN 50174-2                              |
|  | ISO/IEC 11801                              |
| Ambient Air Temperature For<br>Operation | -560 °C                                    |

### **Packing Units**

| Unit Type Of Package 1       | PCE     |
|------------------------------|---------|
| Number Of Units In Package 1 | 1       |
| Package 1 Height             | 4 cm    |
| Package 1 Width              | 14.4 cm |

| Package 1 Length | 100 cm   |
|------------------|----------|
| Package 1 Weight | 1.803 kg |

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance

| <b>Ø</b> | Reach Free Of Svhc         |     |
|----------|----------------------------|-----|
| <b>⊘</b> | Toxic Heavy Metal Free     |     |
| <b>⊘</b> | Mercury Free               |     |
| <b>⊘</b> | Rohs Exemption Information | Yes |

#### **Certifications & Standards**

| Reach Regulation         | REACh Declaration   |
|--------------------------|---|
| Eu Rohs Directive        | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration            |
| China Rohs Regulation    | China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure | Product Environmental Profile   |
| Circularity Profile      | No need of specific recycling operations  |