



Main

Range	Lisse
Aesthetic name	Screwless deco
Product or component type	Dimmer
Device presentation	Complete product
Load type	230 V AC LED lamp: 5...100 W Incandescent lamp: 25...100 W Halogen lamp: 25...100 W
Colour tint	Mocha bronze
Quantity per set	Set of 1

Complementary

Device mounting	Wall mounted
Dimmer application	Inductive load Resistive load
[Ue] rated operational voltage	230 V AC 50 Hz
Number of gangs	1 gang
Connections - terminals	Screw terminals
Fixing mode	Concealed screws
Material	Stainless steel
Type of packing	Bag
Height	87 mm
Width	87 mm
Depth	44 mm
Product weight	0.129 kg

Environment

Standards	BS EN 60669-2-1
IP degree of protection	IP20

Offer Sustainability

EU RoHS Directive	Not applicable, out of EU RoHS legal scope
-------------------	--

Contractual warranty

Warranty	18 months
----------	-----------
