

Specifications



404918374

GGBL7072C5BSBS

EAN Code: 3606481242891

Complementary

Number Of Gangs	2 gangs
Communication Network Type	RJ45
Fixing Mode	Concealed screws
Connections - Terminals	Screw terminals
Material	Stainless steel
Type Of Installation	Indoor
Depth	39 mm
Width	87 mm
Height	87 mm
Net Weight	0.12 kg

Standards	ANSI/TIA-568-C.2
Ip Degree Of Protection	IP20

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.000 cm
Package 1 Width	8.700 cm
Package 1 Length	8.700 cm

Package 1 Weight	134.900 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	5
Package 2 Height	9.800 cm
Package 2 Width	10.000 cm
Package 2 Length	25.000 cm
Package 2 Weight	769.000 g
Unit Type Of Package 3	CAR
Number Of Units In Package 3	100
Package 3 Height	22.000 cm
Package 3 Width	52.000 cm
Package 3 Length	52.000 cm
Package 3 Weight	16.205 kg

Contractual warranty

Warranty	18 months
----------	-----------