

# Product datasheet

Specifications



fuse holder - GK1 - 3 poles - 20 A -  
for fuse NFC 8.5 x 31.5 mm

GK1CF

EAN Code: 3389110256215

❗ Discontinued

## Main

Range	TeSys
Product Name	TeSys GK1
Device Short Name	GK1 C
Fuse Size	8.5 x 31.5 mm
Product Or Component Type	Fuse holder
Poles Description	3P
Network Type	AC DC

## Complementary

Network Frequency	50/60 Hz
Control Type	Toggle
Mounting Support	Rail
[Ui] Rated Insulation Voltage	480 V
[Ith] Conventional Free Air Thermal Current	10 A 40 °C with aM cartridge fuses 20 A 40 °C with gG cartridge fuses 20 A 40 °C with tubular links
[Ipk] Rated Peak Withstand Current	8 kA with tubular links conforming to IEC 60269-1
Connections - Terminals	Screw terminals 1 cable(s) 10 mm² flexible without cable end Screw terminals 1 cable(s) 10 mm² solid without cable end Screw terminals 2 cable(s) 6 mm² flexible without cable end Screw terminals 2 cable(s) 6 mm² solid without cable end
Tightening Torque	1.2 N.m - on screw terminals
Operating Position	+/- 23°
Height	81 mm
Width	52.5 mm
Depth	71.5 mm
Net Weight	0.213 kg
Quantity Per Set	Set of 4

## Environment

Standards	IEC 60947-3
Protective Treatment	TC

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ambient Air Temperature For Operation	-50...70 °C
---------------------------------------	-------------

## Contractual warranty

Warranty	18 months
----------	-----------