

Product datasheet

Specifications



Exclusive - rotary dimmer - 2 gangs - white

GLVD2G1W

⚠ Discontinued on: 31 Dec 2016

⚠ Discontinued

Main

Product Or Component Type	Rotary dimmer
Quantity Per Set	Set of 1
Device Presentation	Complete product
Load Type	Low voltage halogen lamp with electronic transformer: 60...250 VA Incandescent lamp
Colour Tint	White matt

Complementary

Device Mounting	Wall mounted
Dimmer Application	Resistive load Inductive load
[Ue] Rated Operational Voltage	230 V AC 50 Hz
Number Of Gangs	2 gangs
Connections - Terminals	Screw terminals
Fixing Mode	By screws M3.5 x 30 mm
Material	Urea (carbamide)
Height	86 mm
Width	86 mm
Depth	17 mm
Net Weight	0.129 kg

Environment

Standards	BS EN 60669-2-1
Ip Degree Of Protection	IP20

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9.3 cm
Package 1 Width	4.8 cm
Package 1 Length	9.3 cm
Package 1 Weight	132 g

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Contractual warranty

Warranty	18 months
----------	-----------