

Product datasheet

Specifications



DOL combination starter , TeSys Deca, 0.63...1 A , 400V AC

GV2DM105V7

EAN Code: 3389110781915

❗ Discontinued

Main

Range Of Product	TeSys Deca
Device Short Name	GV2DM
Product Or Component Type	Motor starter
Motor Starter Type	Non reversing
Coordination Type	Type 1
Poles Description	3P
Utilisation Category	AC-3
Motor Power Kw	0.25 kW at 400/415 V AC 50/60 Hz 0.37 kW at 400/415 V AC 50/60 Hz 0.25 kW at 440 V AC 50/60 Hz 0.37 kW at 440 V AC 50/60 Hz
Magnetic Tripping Current	13 A

Complementary

Device Composition	1 combination block GV2AF3 1 motor circuit breaker type GV2ME 1 3-pole contactor
Thermal Protection Adjustment Range	0.63...1 A
Rated Breaking Capacity	Iq 50 kA at 400/415 V conforming to IEC 60947-4-1 Iq 50 kA at 440 V conforming to IEC 60947-4-1 Iq 50 kA at 500 V conforming to IEC 60947-4-1
Net Weight	0.596 kg
Height	176.4 mm
Width	45 mm
Depth	99.6 mm

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications