



### Main

Range of product	TeSys
Device short name	GV2DM
Product or component type	Motor starter
Motor starter type	Non reversing
Coordination type	Type 1
Poles description	3P
Utilisation category	AC-3
Motor power kW	7.5 kW at 500 V AC 50/60 Hz 5.5 kW at 400/415 V AC 50/60 Hz 5.5 kW at 440 V AC 50/60 Hz
Magnetic tripping current	170 A

### Complementary

Device composition	1 3-pole contactor 1 combination block GV2AF3 1 motor circuit breaker type GV2ME
Thermal protection adjustment range	9...14 A
Rated breaking capacity	Iq 15 kA at 400/415 V conforming to IEC 60947-4-1 Iq 6 kA at 500 V conforming to IEC 60947-4-1 Iq 8 kA at 440 V conforming to IEC 60947-4-1
Product weight	0.601 kg
Height	176.4 mm
Width	45 mm
Depth	99.6 mm

### Contractual warranty

Warranty period	18 months
-----------------	-----------