



# FEED UNIT 40A RIGHT MOUNTING

Local distributor code: 23348163

KBB40ABD4W

EAN Code: 3606480001000

#### Main

Range Of Product	Canalis
Device Short Name	KBB
Product Compatibility	Canalis KBB busbar trunking 2540 A
Offer Type	Classic
Product Or Component Type	Feed unit
Conductors Material	Aluminium
[le] Rated Operational Current	40 A 25 A
[Ue] Rated Operational Voltage	230400 V
Number Of Circuits	1
Busbar Trunking Polarity	3L + N + PE L + N + PE
Protection Type	Without protection
Control Type	Without
Colour	White (RAL 9003)

## Complementary

Provided Equipment	End cover
Mounting Location	Right
Mounting Mode	By clips
Mounting Support	Busbar
Connections - Terminals	Terminal block - Pg 21 - screw clamp connector for 10 mm²
Width	244 mm
Depth	75.5 mm
Height	75.5 mm
Net Weight	500 g
Standards	IEC 61439-6

#### **Environment**

Ip Degree Of Protection IP55 conforming to IEC 60529

## **Packing Units**

Unit Type Of Package 1 PCE

Number Of Units In Package 1	1
Package 1 Height	7.0 cm
Package 1 Width	7.0 cm
Package 1 Length	27.0 cm
Package 1 Weight	464.0 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	15
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	7.876 kg
Unit Type Of Package 3	P06
Number Of Units In Package 3	60
Package 3 Height	44.0 cm
Package 3 Width	60.0 cm
Package 3 Length	80.0 cm
Package 3 Weight	41.752 kg

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

<b>⊘</b>	Reach Free Of Svhc
<b>⊘</b>	Toxic Heavy Metal Free
<b>9</b>	Mercury Free
<b>Ø</b>	Rohs Exemption Information Yes
<b>⊘</b>	Pvc Free
<b>⊘</b>	Halogen Free Product

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations

## **Dimension Drawings**

