



Local distributor code:

23348299

KBB40ABT44W



EAN Code: 3606480001130

### Main

| Range Of Product               | Canalis                            |  |
|--------------------------------|------------------------------------|--|
| Device Short Name              | КВВ                                |  |
| Product Compatibility          | Canalis KBB busbar trunking 2540 A |  |
| Offer Type                     | Classic<br>Control system          |  |
| Product Or Component Type      | Feed unit                          |  |
| Conductors Material            | Aluminium                          |  |
| [le] Rated Operational Current | 40 A<br>25 A                       |  |
| [Ue] Rated Operational Voltage | 230400 V                           |  |
| Number Of Circuits             | 2                                  |  |
| Busbar Trunking Polarity       | 3L + N + PE<br>L + N + PE          |  |
| Protection Type                | Without protection                 |  |
| Control Type                   | Communicating                      |  |
| Communication Port Protocol    | DALI                               |  |
| Colour                         | White (RAL 9003)                   |  |

# Complementary

| Provided Equipment      | End cover  |  |
|-------------------------|--|--|
| Mounting Location       | Central  |  |
| Mounting Mode           | By clips   |  |
| Mounting Support        | Busbar   |  |
| Connections - Terminals | Terminal block - Pg 21 - screw clamp connector for 610 mm² |  |
| Width                   | 244 mm   |  |
| Depth                   | 103.5 mm   |  |
| Height                  | 75.5 mm  |  |
| Net Weight              | 500 g  |  |
| Standards               | IEC 61439-6  |  |

### **Environment**

Ip Degree Of Protection IP55 conforming to IEC 60529

# **Packing Units**

| Unit Type Of Package 1       | PCE     |
|------------------------------|---------|
| Number Of Units In Package 1 | 1       |
| Package 1 Height             | 9.0 cm  |
| Package 1 Width              | 22.0 cm |
| Package 1 Length             | 64.0 cm |
| Package 1 Weight             | 3.25 kg |
| Unit Type Of Package 2       | P06     |
| Number Of Units In Package 2 | 22      |
| Package 2 Height             | 80.0 cm |
| Package 2 Width              | 80.0 cm |
| Package 2 Length             | 60.0 cm |
| Package 2 Weight             | 80.0 kg |

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance

| <b>⊘</b> | Reach Free Of Svhc                 |     |
|----------|------------------------------------|-----|
| <b>⊘</b> | Toxic Heavy Metal Free             |     |
| <b>⊘</b> | Mercury Free                       |     |
| <b>⊘</b> | Rohs Exemption Information         | Yes |
| <b>⊘</b> | Halogen Free Plastic Parts Product |     |

### **Certifications & Standards**

| Reach Regulation         | REACh Declaration   |
|--------------------------|---|
| Eu Rohs Directive        | Compliant EU RoHS Declaration   |
| China Rohs Regulation    | China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)                                   |
| Environmental Disclosure | Product Environmental Profile   |
| Weee                     | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |
| Circularity Profile      | No need of specific recycling operations  |