

Product datasheet

Specifications

STRAIGHT LENGTH 63 A

Local distributor code:

389354464

KNT63ED4303



EAN Code: 3606480003448

Main

Range Of Product	Canalis
Product Name	KN
Product Or Component Type	Straight length
Device Application	Low power distribution
[Ie] Rated Operational Current	63 A at 35 °C
Busbar Trunking Polarity	3L + N + PE 3L + PEN
Number Of Tap-Off Outlets	3
Length	3 m

Complementary

[Ue] Rated Operational Voltage	230...500 V
Network Frequency	50/60 Hz
[Uimp] Rated Impulse Withstand Voltage	6 kV
[Ui] Rated Insulation Voltage	500 V
[Icw] Rated Short-Time Withstand Current	1.4 kA
[Ipk] Rated Peak Withstand Current	11 kA
Electrical Connection	Lubricated sliding contact
Radiated Magnetic Field	0.063 μ T
Thermal Stress Limit	1980 kA ² .s
Thdi	0...15 % 63 A 15...33 % 50 A 33...100 % 40 A
Maximum Voltage Drop	<0.178 V with power factor = 1 at 50 Hz with 1A for 100 m long <0.169 V with power factor = 0.9 at 50 Hz with 1A for 100 m long <0.155 V with power factor = 0.8 at 50 Hz with 1A for 100 m long <0.140 V with power factor = 0.7 at 50 Hz with 1A for 100 m long
Mounting Mode	By screws
Neutral Position	Up
Number Of Circuits	1
Control Type	Communicating
Standards	IEC 61439-6
Width	92 mm
Depth	27.5 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Colour	White (RAL 9001)
Net Weight	5.7 kg

Environment

Ip Degree Of Protection	IP55 conforming to IEC 60529
Ik Degree Of Protection	IK08 conforming to IEC 62262
Ambient Air Temperature For Operation	0...35 °C (100 % of In) 35...40 °C (97 % of In) 40...45 °C (94 % of In) 45...50 °C (91 % of In) 50...55 °C (87 % of In)

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.500 cm
Package 1 Width	10.000 cm
Package 1 Length	310.000 cm
Package 1 Weight	5.000 kg
Unit Type Of Package 2	BB1
Number Of Units In Package 2	4
Package 2 Height	11.000 cm
Package 2 Width	16.000 cm
Package 2 Length	314.000 cm
Package 2 Weight	22.000 kg
Unit Type Of Package 3	PAL
Number Of Units In Package 3	48
Package 3 Height	45.000 cm
Package 3 Width	65.000 cm
Package 3 Length	320.000 cm
Package 3 Weight	281.000 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability






Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

 Reach Free Of Svhc	
 Toxic Heavy Metal Free	
 Mercury Free	
 Rohs Exemption Information	Yes
 Halogen Free Product	
Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins