



Main

Range	Acti 9
Product name	Acti 9 SBI
Product or component type	Fuse-disconnector
Device short name	SBI
Poles description	1P + N

Complementary

[In] rated current	10 A 16 A 20 A 25 A 32 A 12 A 40 A 50 A
Fuse curve	AM GG
Fuse size	14 x 51 mm
[Ue] rated operational voltage	690 V AC
Mounting support	35 mm symmetrical DIN rail
9 mm pitches	6
Connections - terminals	Screw clamp terminals1 cable(s) 2.5...25 mm ² rigid Screw clamp terminals1 cable(s) 2.5...25 mm ² flexible
Tightening torque	3.5 N.m

Environment

Standards	IEC EN 60947-3
Pollution degree	3
Ambient air temperature for operation	-20...60 °C
Ambient air temperature for storage	-40...80 °C

Offer Sustainability

REACH Regulation	REACH Declaration
------------------	-----------------------------------

EU RoHS Directive	Under investigation EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	Download RoHS China Declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------